

## PB270-2 Bath Fan w/ 2x Grill

6" remote bath fan, two 4" grilles w/o light, 270 cfm

Item #: 40572

Variant: 120V 1~ 60Hz



PB270-2 remote inline bath fan connects two separate bathrooms to one central exhaust point and removes moisture from the air with virtually no noise. With a small footprint on the bathroom ceiling, the white unobtrusive exhaust grilles easily fit any bathroom design.

- Airflow 260 CFM at 0.20" Wg.
- Smallest footprint on ceiling
- Two locations
- Two 7" white round plastic grilles
- Remote mount 6" duct fan
- Backdraft dampers included
- ENERGY STAR® listed
- UL listed for wet locations

The fan motor is located away from the bathroom which enables virtually silent operation. The ceiling exhaust grilles are tied to the fan motor via an insulated flexible duct. The grilles can be located over the toilet, the shower or above any other source of moisture or odor.

PB270 fan consists of a 6" fan, two ceiling vent grilles and grille housings with backdraft dampers. The grilles use a 4" duct, the fan uses a 6" duct. The fan is designed for intermittent or continuous operation to meet ASHRAE Standard 62.2. UL listed for wet locations. Configurations with LED lights are available.

