

FIDT 8 Insulated Flex Duct

8" flexible duct, R4.2 Rating, 25ft

Item #: [411065](#)

- R4.2 fiberglass insulation
- Air-tight inner core
- Low friction
- Tear and puncture metallized polyester jacket

FIDT are insulated flexible ducts for indoor use in residential and commercial HVAC systems with low-to-medium operating pressure. Ducts are manufactured with a tri-directional fiberglass scrim reinforced, metallized polyester outer jacket. R4.2 value. Available in 25 ft length. UL 181 certified.

