

## FADE 20-43 3ph. Axial Fan

20" Axial Fan, 4 Pole, 4929 cfm, 208-460V, 3~

Item #: [45297](#)

Variant: 230(208-230)V 3~ 60Hz

- Shallow profile with no protruding motor
- Maximum inlet temperature is 158°F

### Application

Fantech's FADE Series axial fans are designed to effectively and quietly handle major ventilation challenges in locations such as large warehouses without taking up a lot of valuable space.

### Design

All FADE Series fans combine aerodynamically designed propeller blades and an external rotor motor expertly integrated into one unit. Fans feature a heavy gauge galvanized steel and powdercoated finish casing. With fan sizes ranging from 8" to 25", Fantech's FADE Series fans move a lot of air, yet are statically and dynamically balanced for vibration-free operation. The external rotor motorized propeller provides excellent heat dissipation, even at low RPM. Rated for continuous duty.

