

## FADE 25-63 WHD 3ph. Axial Fan

25" Axial Fan w/Assembled Housing and Damper, 230-460V, 3~

Item #: [45432](#)

Variant: 460V 3~ 60Hz

- 100% speed-controllable
- Shallow profile with no protruding motor
- All fans include motor side guards as standard
- Three-year warranty
- UL Listed and AMCA Certified
- Airflow temperature up to 140°F

Fantech's FADE Series axial fans are designed to effectively and quietly handle major ventilation challenges in locations such as large warehouses without taking up a lot of valuable space.

All FADE Series fans combine aerodynamically designed propeller blades and rotor motor into one expertly integrated unit. Fans feature a heavy gauge galvanized steel and powdercoated finish casing. With fan sizes ranging from 8" to 25", Fantech's FADE Series fans move a lot of air, yet are statically and dynamically balanced for vibration-free operation. The external rotor motorized propeller provides excellent heat dissipation, even at low RPM. Rated for continuous duty.

