

AEV80 Air Exchanger

w/o heat recovery, 82 cfm, 120V, 1~

Item #: 463843



- Airflow up to 82 cfm @ 0.2" PS serves 1-2 bedroom homes
- Washable MERV8 synthetic filter
- Unit can be installed in any position
- External three position switch (Low/Standby/Medium)

Suitable for temperate climates where balanced ventilation is needed, an Air Exchanger Ventilator (AEV 80) is designed to provide fresh air into a building while exhausting an equal amount of stale air. During the winter months, the incoming cold fresh air is warmed by mixing it with return air before it is supplied to the home. During summer months when the indoor space is air conditioned, the AEV will help in cooling the incoming fresh air with the stale air that is being exhausted.

The unit runs continuously or on intermittent, giving the homeowner complete control over the air quality. Continuous low speed ventilation is recommended, which will help eliminate carbon dioxide, volatile organic components (VOC's) and other gases as well as freshen up the home. Intermittent high speed ventilation can be obtained through a variety of option remote controls. Dehumidistat MDEH1 comes with the air exchanger.

