

1ACC24MD Motorized Damper

24" motorized wall damper

Item #: [47011](#)

Manufactured from 14-gauge galvanized steel frame 2" deep with 1" flange. For quiet operation steel blades have felted edges. Damper is equipped with a motor to open and a spring return to close. Maximum airflow is 3500 FPM. 120/240V, 0.19/0.11A, 60 Hz. 54MD and 60MD models are 240V only.

