

## 5ADE12BA Axial Exh Roof Fan

12" Dir Drive Axial Roof Exh Fan, 1,423 cfm, 1/4 HP, 120V

Item #: 47244

Variant: 120V 1~ 60Hz



- All ventilators are UL 705 Standard listed
- Inlet temperatures up to 140°F
- Junction box mounted in motor compartment
- Built-in bird screen to protect discharge and ensure safe operation
- Externally cooled motor compartment
- Speed controllable

Direct-drive axial roof ventilators are designed for use in applications requiring the steady exhaust of air under low to moderate static pressures. All models are manufactured from durable spun aluminum; venturi, inlet and supports are galvanized. Blades are made from stamped aluminum. Ventilators are wall mountable.

