

5DDU10AA Upblast Roof Fan

10.5" Roof Ventilator Direct Drive Upblast 1/6 HP, 120V

Item #: 47335

Variant: 115V 1~ 60Hz



- All ventilators are listed UL 705
- All ventilators except 5DDU 085AY are UL 762 listed
- Inlet temperatures up to 300°F
- Backward inclined aluminum fan wheel
- Externally cooled motor compartment
- Fully welded windband

Direct-drive upblast ventilators are designed for continuous operation to exhaust foul air, smoke, fumes, odors and grease-laden vapors from range hoods and commercial cooking appliances. Ventilators are designed for installation in industrial, institutional and commercial kitchen applications. All models are equipped with a backward inclined aluminum fan wheel and a speed controllable motor.

