

## 5DDD085A w/BS D/blast Roof Fan

8 " Direct Drive Downblast, .55 HP, 1650 RPM, 120V, w/BS

Item #: 47386

Variant: 115V 1~ 60Hz



- All ventilators are UL 705 Standard listed
- One-piece removable exhaust hood
- Inlet temperatures up to 170°F
- Backward inclined aluminum fan wheel
- Equipped with a built-in bird screen to protect discharge
- Externally cooled motor compartment

### Application

Direct-drive downblast ventilators are designed for use where steady exhaust ventilation is needed under low to moderate static pressure conditions. Ventilators can be mounted on the roof or wall.

### Design

All models are equipped with a backward inclined aluminum fan wheel and a speed controllable motor.

### Certification

All models are UL 705 listed.

