

5DDD10AA w/BS D/blast Roof Fan

10.5" Direct Drive Downblast, 1/6 HP, 1720 RPM, 120V, w/BS

Item #: 47388

Variant: 115V 1~ 60Hz



- All ventilators are UL 705 Standard listed
- One-piece removable exhaust hood
- Inlet temperatures up to 170°F
- Backward inclined aluminum fan wheel
- Equipped with a built-in bird screen to protect discharge
- Externally cooled motor compartment

Application

Direct-drive downblast ventilators are designed for use where steady exhaust ventilation is needed under low to moderate static pressure conditions. Ventilators can be mounted on the roof or wall.

Design

All models are equipped with a backward inclined aluminum fan wheel and a speed controllable motor.

Certification

All models are UL 705 listed.

