

IPF05 Speed control

1-gang box mount, w/ decora plate, 120V, 5A

Item #: 484164

Variant: 115V 1~ 60Hz



IPF05 Fan Speed Control features a low-profile fluid slide bar movement for fine adjustment of fan speeds. Easy-to-use ON/OFF preset switch controls the fan without disturbing your favorite pre-selected settings. Built-in LED locator light illuminates when the load is off. Designed for both single-pole (one-location) and 3-way (multi-location) applications. RFI noise suppression. Ivory and Light Almond color change kits included.

IPF05 was sold as 6637-PW in the past.

