

## Rn1 Inline Radon Fan

4.5" pipe, plastic housing, 0.9" max SP

Item #: 89051

Variants: 120V 1~ 60Hz

This product has been discontinued

This product was replaced by [Rn1 Inline Radon Fan](#)



Rn1 Radon Fan is designed for active radon mitigation systems to employ for applications where low suction and low flow are needed. It is a perfect choice for low Radon levels and good sub-slab communication. Rn1 replaces HP2133 and FR100 (Radon) models.

- Designed specifically for Active Soil Depressurization (ASD) mitigation applications
- Low suction, low flow
- For residential applications
- Air-tight housing - zero leakage
- UV resistant plastic housing
- UL Listed for safety and outdoor use
- HVI certified fan performance
- ENERGY STAR® listed
- 5-year factory warranty

Manufactured from two molded plastic pieces seamlessly joined together. It is inherently and permanently airtight ensuring no Radon leakage. A large watertight electrical wiring enclosure ensures electrical installation quick and simple. Fan motor is thermal overload protected with automatic reset and can be installed both indoors or outdoors. To simplify installation on a 3" or 4" PVC pipe, use FRIK 4x3 or FRIK 4x4 Installation kits.

