

Rn3 Inline Radon Fan

Radon Fan, Inline, 6" PVC pipe, 2.6" max Ps

Item #: 89053

Variant: 120V 1~ 60Hz



Rn3 Radon Fan is designed for active radon mitigation systems to employ for applications where medium suction and medium flow are needed. It is a perfect choice for elevated Radon levels and poor communication, multiple suction points and/or large sub slab footprint. Rn3 replaces HP220, FR150 (Radon), and FR160 (Radon) models.

- Designed specifically for Active Soil Depressurization (ASD) mitigation applications
- Medium suction, medium flow
- For residential applications
- Air-tight housing - zero leakage
- UV resistant plastic housing
- UL Listed for safety and outdoor use
- HVI certified fan performance
- 5-year factory warranty

Manufactured from two molded plastic pieces seamlessly joined together. It is inherently and permanently airtight ensuring no Radon gas leakage. A large watertight electrical wiring enclosure ensures electrical installation quick and simple. Fan motor is thermal overload protected with automatic reset and can be installed both indoors or outdoors. To simplify installation on a 3" or 4" PVC pipe, use FRIK 6x3 or FRIK 6x4 Installation kits.

