

# PRO PLUS-L Exhaust Fan

Bath Fan, Surface Mount, 2 Sensor Grille w/ LED, 140 cfm, 6"

Item #: 98507



- Less than 0.5 Sones
- LED Light
- Motion and Humidity Sensors
- Built-in backdraft damper
- High efficiency motor
- 5 year warranty

## Application

The PRO PLUS-L exhaust fan provides remarkably quiet, energy efficient ventilation for bathrooms, powder rooms and other areas with square footage up to 130 sq. ft. The fan is designed for intermittent or continuous operation to meet **ASHRAE Standard 62.2**.

## Model

140 cfm fan with a ceiling grille, 11W LED light, humidity and motion sensor, backdraft damper. The fan provides 4 different airflows: 80-90-110-140 cfm. Uses a 6" flexible duct. The product is provided with an adjustable 12-24" bar hanger for ease of installation.

This model holds an ETL listing. ENERGY STAR® and HVI qualified, California Title 24 Listed.

