

Bathroom Ventilation

Ceiling Grilles and Bulbs for Premium Bath Fans



PBV
Ceiling Grille and Housing
Includes damper and four hange bars. Fits between 2x6 (PBV 4) or 2x8 (PBV 6) construction. Available in 4 and 6 inch duct sizes

PBV4
3 lbs



PBL
Ceiling Grille and Housing with a dimmable LED light
Includes damper, four hanger bars, and a dimmable 10W LED bulb. Fits between 2x6 construction. Available in 4 inch duct size.

PBL104
4 lbs

PBB
Replacement Bulbs for PBL and PBH grilles

PBB L10-ES are dimmable LED bulbs, 3000K, E26 base, wet location, ENERGY STAR®. Use with PB(W)xxx L10 bathroom fans and PBL10 ceiling grilles. All replacement packs include 6 bulbs.

PBB50 is a dimmable halogen bulb, GU10 base, wet location. Use with PB(W) 110H, PB 270H-2, PB 270HV-2 bathroom fans and PBH ceiling grilles.



PBB Halogen
50 pack
(Replacement Only)

PBB L10
10 pack



Switches and Controls for Ventilation

Speed Control for AC-motor Fans



WC 15
Multipurpose Speed Control
Rotary type variable speed controller with on/off switch is designed for mounting in a 2" X 4" electrical wall box. Important features, such as RFI (radio frequency interference) filter, minimum speed trimpot, and built-in On/Off Line Switch are standard. All leads are approximately 6" long and stripped 1/2". Brushed aluminum switch plate and screws included. Fits standard single gang box.

WC 15
120 V, 5A max
1 lbs



RPE
Multipurpose Speed Control
Heavy duty rotary type variable speed controller with on/off switch. The product is designed for mounting in a wall. Important features, such as RFI (radio frequency interference) filter, Minimum speed trimpot, and built-in On/Off Line Switch are standard. All leads are approximately 6" long and stripped 1/2".

RPE 10 120V, 10A max 1 lbs
RPE 15 120V, 15A max 1 lbs
RPE 210 230V / 1 phase, 10A max 1 lbs

Switches and Controls for Ventilation

Controls for EC-motor Fans



MTP 10
Potentiometer for Manual Speed Control
May be surface mounted for manual speed control of all EC-motor fan models. Input is 10Vdc / Output is 0-10Vdc.

MTP 10
0-10 V
.5 lbs

Speed control selection guide

Solid State Speed Control ¹ for AC-motor Fans				
Model	Type	Voltage, V	Current, A	Use With Fan Models
WC 15	Rotary w/ On-Off	120	5	AC-motor fans with 100% speed-controllable motors. Fan models include PB & PBW bath fans, prioAir (AC models), RVF, FG, FR, CVS, FKD, RE(C), FADE, FRD, and FSD
RPE 10	Rotary w/ On-Off	120	10	
RPE 15	Rotary w/ On-Off	120	15	
RPE 210	Rotary w/ On-Off	230	10	

¹ Select speed control model for correct voltage and sufficient current capacity.
² Some commercial fan model sizes require speed control with greater current capacity (amperage) than is available with these accessory speed control models. Speed control for such fan model sizes must be furnished by others.
³ Not all 2SHE models are compatible with speed control; check specific fan model for suitability.