

**0024** € 30,10

**HOT AIR GUN**



Box



Temperature	300 °C - 500 °C
Air stream	280 l/min - 480 l/min
Power	230 V 50Hz 1,5 kW

€ 24,20

**0441** € 69,90

**HOT KNIFE FOR POLYSTYRENE WITH ADJUSTABLE TEMPERATURE**

For polystyrene, plastic, foam and sponge, adjustable cutting length, metal stand



Box



€ 57,10

Power	230 V, 50 Hz, 220 W
Temperature	120 - 220 - 330 - 400 - 450 °C
Cutting capacity with adjustment	20 ÷ 90 mm
Max cut	150 mm

**0333** PRO € 111,00

**HOT KNIFE FOR POLYSTYRENE WITH ADJUSTABLE TEMPERATURE**

For polystyrene, plastic, foam and sponge, adjustable cutting length, metal stand



Carrying case



€ 86,30

Power	230 V, 50 Hz, 150 W
Temperature	Max 500 °C
Max cut	150 mm

**0677** € 41,00

**HAND OPERATED LEVER GREASE GUN**

Composed of metal tank and pump, coupler and 450mm PVC flexible hose for using ø 55mm grease cartridges or loose grease (adaptor already mounted).



Box



€ 33,30

Capacity	1000 cc
Flexible hose sizes	ø 9 x 450 mm

**0444** PRO € 84,00

**DIGITAL HOT AIR GUN SET**

With electronic temperature control, lcd display to show the temperature, 2 levels of air flow, ideal for heating, folding, bending, removing paint



6 Pcs



Box

ABS



€ 68,90

Power	230 V, 50 Hz, 2000 W
Temperature	I 70°C - II 70°C ÷ 600°C - III 70°C ÷ 600°C
Air stream	I 300L/min - II 300L/min - III 500L/min

**0321** € 47,60

**HOT KNIFE FOR POLYSTYRENE WITH ADJUSTABLE TEMPERATURE**

For polystyrene, plastic, foam and sponge, adjustable cutting length.



Box



€ 37,10

Power	230 V, 50 Hz, 130 W
Temperature	Max 450 °C
Cutting capacity with adjustment	14 ÷ 97 mm
Max cut	120 mm

**0677/500** € 18,00

**500CC HAND OPERATED LEVER GREASE GUN**

Composed of metal tank and pump, coupler and 300mm PVC flexible hose, for using with loose grease or ø 53mm grease cartridges.



Box



€ 14,80

Capacity	500 cc
Flexible hose sizes	ø 8 x 300 mm
Working pressure	6000-8000 psi

**0189-**

**METAL FUEL TANK**

With flexible filler, "un" certified according to european directives



a partire da € 29,20

Capacity Liters	Net weight	Art.	€	Promo
5	1,5 kg	0189/05C	€ 42,30	€ 29,20
10	2,5 kg	0189/10C	€ 42,90	€ 32,20
20	3,7 kg	0189/20C	€ 48,90	€ 32,80