

0567

€ 103,00

LOW PROFILE HYDRAULIC TROLLEY JACK

2 tons, made of steel



€ 81,40

Capacity	2 ton
Lifting	90 ÷ 385 mm
Dimensions	580 x 165 x 235 h mm
Net weight	13 kg

0375A

€ 295,00

LOW PROFILE HYDRAULIC TROLLEY JACK

2,5 ton, double pump quick lift, with load limiter.



€ 224,00

Capacity	2.5 ton
Lifting	75 ÷ 500 mm
Dimensions	680 x 345 x 220 h mm
Net weight	32,5 kg

0060

€ 76,10

HYDRAULIC TROLLEY JACK

Metal body frame. Handle for hand carrying. Extendable lever.



€ 60,10

Capacity	2 ton
Dimensions	535 x 225 x 145 mm
Lifting	135 ÷ 385 mm
Net weight	11 kg

C039/15

€ 228,00

HYDRAULIC TROLLEY JACK

Aluminium and steel hydraulic trolley jack with double pump



€ 173,00

Capacity	1,5 ton
Dimensions	490 x 270 x 130 h mm
Lifting	90 ÷ 358 mm
Net weight	15 kg

0369

€ 358,00

HYDRAULIC TROLLEY JACK

Dual pump, with removeable saddle and rubber pad



€ 289,00

Capacity	3,5 ton
Dimensions	745 x 335 x 180 mm
Lifting	110 ÷ 560 mm
Net weight	46 kg

0065A

€ 249,00

HYDRAULIC TROLLEY JACK

With removable saddle.



€ 199,00

Capacity	3 ton
Dimensions	660 x 345 x 260 mm
Lifting	140 ÷ 515 mm
Net weight	33 kg

C039/25

€ 315,00

HYDRAULIC TROLLEY JACK

Aluminium and steel hydraulic trolley jack with double pump



€ 240,00

Capacity	2.5 ton
Dimensions	659 x 289 x 165 h mm
Lifting	110 ÷ 460 mm
Net weight	27 kg

0658

€ 858,00

HYDRAULIC JACK

€ 679,00

Capacity	10 ton
Lifting range of foot	30 ÷ 260 mm
Lifting range of head	420 ÷ 665 mm
Net weight	30 kg