

0517A
€ 868,00
THICKNESSER

With working plate made of granite

Dimensions	710 x 640 x 400 mm
Working table dimensions	330 x 238 mm
Arbor	ø 51.5 mm
Blade	2
Thickness capacity	330 x 2.4 x 152 mm
Spindle speed	8500 rpm
Motor	230 V 50 Hz 1.5 kW
Net weight	35 kg


€ 668,00
0686/200
€ 592,00
COMBINED PLANER AND THICKNESSER

With aluminum working tables

Dimensions	770 x 430 x 450h mm
Tables height	360 mm
Table dimensions	737 x 210 mm
Arbor	ø 50 mm
Blade	N° 2
Planer capacity	204 x 2 mm
Thickness capacity	204 x 2 x 120h mm
Spindle speed	8000 rpm
Motor	230 V 50 Hz 1,25 kW
Net weight	25 kg


€ 465,00
0665
€ 3240,00
PARTIALLY ASSEMBLED PANEL SAW

Blade	250 x 3 x 30 mm Z 40
Blade speed	2800 rpm
Main table dimensions	800 x 560 mm
Extension table dimensions	800 x 305 mm
Working height	860 mm
Max cut depth at 45°	60 mm
Max cut depth at 90°	75 mm
Sliding table	500 x 600 mm
Overall dimensions	1860 x 2030 x 1070h mm
Motor	230 V 50 Hz 2,2 kW
Max cutting length with saw bench	1460 mm
Net weight	230 kg


€ 2550,00
0656/254
€ 2700,00
PANEL SAW

Capacity 254mm, partially assembled.

Blade dimensions	254 x 30 x 3,2 mm 40 T
Blade speed	4000 rpm
Main table dimensions	790 x 350 mm
Extension table dimensions	350 x 350 mm
Working height	850 mm
Cutting depth at 90°	80 mm
Cutting depth at 45°	56 mm
Sliding table	1320 x 238 mm
Motor	230 V 50 Hz 2,2 kW
Max cutting length with saw bench	1250 mm
Net weight	150 kg


€ 2060,00
0656/310
€ 3110,00
PANEL SAW

Capacity 315mm, partially assembled.

Blade dimensions	315 x 30 x 3,2 mm 40 T
Blade speed	4000 rpm
Main table dimensions	790 x 350 mm
Extension table dimensions	350 x 350 mm
Working height	850 mm
Cutting depth at 90°	100 mm
Cutting depth at 45°	70 mm
Sliding table	1320 x 238 mm
Motor	230 V 50 Hz 2,2 kW
Max cutting length with saw bench	1400 mm
Net weight	175 kg


€ 2420,00
0871
€ 617,00
SLIDE COMPOUND MITRE SAW

With laser beam indicator of the cutting line.

Saw blade	ø 305 x 30 x 3,2 mm Z 40
Max cutting capacity 0° - 90°	340 x 100 mm
Max cutting capacity 45° - 90°	240 x 100 mm
Sliding travel	215 mm
Motor	230 V 50 Hz 2 kW
Motor speed	4500 rpm
Net weight	25 kg


€ 491,00
0870/250
PRO € 435,00
MITRE SAW

With upper table for usage as saw bench

Saw blade	ø 250 x 30 x 2,5 mm Z 36
Max cutting capacity 0° - 90°	75 x 130 mm
Max cutting capacity 45° - 45°	75 x 50 mm
Max cutting capacity 45° - 90°	75 x 90 mm
Max cutting capacity 0° - 45°	50 x 130 mm
Max cutting capacity, upper table	40 mm
Motor	230 V 50 Hz 1,8 kW
Motor speed	4500 rpm
Peripheral speed disc	59 m/s
Net weight	15,5 kg


€ 299,00
0855
€ 1030,00
WOOD BAND SAW

Saw wheel	ø 315 mm
Blade	2240 x 16 x 0,52 mm T4
Cutting capacity	300 x 155 mm
Table dimensions	400 x 500 mm
Cutting speed	6 - 12 m/s 370 - 800 rpm
Tilting table	0 ÷ 20°
Working height	1010 mm
Motor	230 V 50 Hz 0,75 kW
Dimensions	650 x 650 x 1610 h mm
Net weight	75 kg


€ 819,00