

0430

€ 266,00

**MOTORCYCLE DOLLY**

Powder coated steel. It is suitable for motorcycles and scooters that have the side stand. It allows you to move and to park your bike in tight spaces



Maximum capacity	300 kg
Length	1929 mm
Net weight	33 kg

€ 221,00

S017

€ 230,00

**UNIVERSAL TELESCOPIC CART**

Adjustable in height and length, made of square steel pipes, after use it can be stored in small space, upper sides with rubber to prevent scratches and give more stability to the leaned object, 4 swivel casters of which 2 with brake, ideal for the car body repair, for repairing and spraying area



Height min - max	840 ÷ 1320 mm
Length	225 ÷ 1380 mm
Width	860 mm
Capacity	100 kg
Net weight	26 kg

€ 185,00

0217

€ 206,00

**VEHICLE POSITIONING JACK**

With wheel positioning brakes.



Capacity	680 kg
Lateral stroke	370 mm
Working range	710 - 340 mm
Max tire width	325 mm
Overall dimensions	730 x 468 x 440h mm
Net weight	15 kg

€ 157,00

0645/S

€ 56,70

**SHOP SEAT**

With pivoting wheels, tool holder base, seat with padding



Box

Dimensions	368 x 360 x 365 mm
Net weight	3,8 kg

€ 41,70

0645/CC

€ 95,60

**THREE-DRAWER CAR SEAT**

Equipped with 3 drawers with bearings, 3 can trays and a small frontal tray, 4 pivoting wheels



Box

Dimensions	370 x 400 x 367h mm
Drawer dimensions	3 - 150 x 300 x 40 h mm
Net weight	8 kg

€ 70,60

0645/CP

€ 70,50

**PLASTIC CREEPER**

Shockproof, with 6 wheels.



Box

Dimensions	1000 x 470 x 120h mm
Net weight	4,8 kg

€ 54,70

0645/C

€ 63,30

**6 WHEELS CAR CREEPER**

Box

Dimensions	1030 x 420 x 110h mm
Net weight	6,5 kg

€ 50,80

0645/SS

€ 69,60

**6 WHEELS CAR CREEPER**

Dimensions	1030 x 420 x 110h mm
Net weight	6,5 kg

€ 55,50