

0693A **PRO** € 84,00

RECHARGEABLE LED LAMP

With charging station, foldable, hanging and magnetic



Battery	3,7V - 2600mAh - Li-ion
LED	6W COB LED - 1W SMD 6500K
Luminous flux	600 lm
Recharging time	4h
Autonomy	4,5h Eco mode
Working temperature	-10°C ÷ 40°C



0401 **PRO** € 73,10

COB LED TECHNOLOGY RECHARGEABLE LAMP

High capacity lithium battery for long time operation, magnetic back for hand-free application, flexible standing arm for multi-angle lighting purposes, strong light output 180 lumens.



Power	100 ÷ 240 V, 50 ÷ 60 Hz
Battery	3,7 V - 2600 mAh - Li-ion
Recharging time	6 h
Autonomy	3,5 h
Intensity	180 lm



0123 € 61,60

MULTIFUNCTION USB RECHARGEABLE LED LIGHT

With front torch with various steps of brightness, lateral white and red LEDs with flashing function. Usb recharging cable and transformer. Charge and recharge status Led. It can be charged directly from a computer.



Battery	3.7V - 1800 mAh - Li-ion
LED	24 Cree XPG R5
Intensity	30 - 300 lm
Dimensions	191 x 99 x 148 mm
Battery charger	USB 110 - 230 V 50 - 60 Hz
Autonomy	2,5 h



G900 € 14,60

CAMPING LANTERN



Dimensions	Ø 60 x 160 mm
Intensity	150 lm
Not included batteries	3 x AAA

€ 11,00

0445/20 **PRO** € 156,00

RECHARGEABLE LED FLOODLIGHT

With switch, adapters to recharge batteries with car dc lighter and home ac 230V.



Power	DC 12 - 24 V, 20 W; AC 230 V 20W
Luminous flux	600 - 1450 lm
Battery	7.4V 5400mAh Li-ion
Autonomy	1,5 h



0900 **PRO** € 84,00

MULTI PORTABLE MAGNETIC LED LIGHT

COB Led portable lamp made in impact-resistant ABS. Adjustable in four different light intensities from 350 to 1400 Lumen. The strong magnet at the base and the rotatable body through 180°, makes it perfect to be used in any circumstance.



LED	COB
Power	USB Type C 5 V 2 A
Battery	3.7 V 5200 mAh Li-ion
Luminous flux	350 ÷ 1400 lm
Recharging time	4 h
Autonomy	3 h ÷ 14 h
Dimensions	116 x 101 x 41.5 mm



0900/BL **PRO** € 235,00

MAGNETIC LED LAMP WITH EXTENDABLE UNDERCABINET STAND

The under-hood lamp consists of two magnetic, 360-degree rotatable Cob Led light points for a maximum of 2800 lumens (1400lm + 1400lm) and an extendable bar up to 2100mm to fit any type of hood.



LED	COB
Power	USB Type C 5 V 2 A
Luminous flux	2 x 400-1400 lm
Recharging time	4 h
Autonomy	4 h
Adjustable extension clamps	850 ÷ 2100mm



0621/A3 € 107,00

AUTO RE-ENTERING CABLE REEL



Cable length	10 m
Cable type	3 x 1,50 mm2 H05VV-F



Power	12 V ÷ 240 V
Max power for rolled cable	1200 W
Max power for unrolled cable	1800 W