

D018 PRO € 4660,00

HARDNESS TESTING MACHINE

Motorized, rockwell, brinell and vickers



Wooden Box

Test force 294,2 N / 306,5 N / 588,4 N / 612,9 N / 980,7 N / 1471 N / 1839 N; 30 kgf / 31,25 kgf / 60 kgf / 62,5 kgf / 100 kgf / 150 kgf / 187,5 kgf

MEASURE UNITS:

| | |
|-----|------------|
| HBS | 4 - 450 |
| HRB | 20 - 100 |
| HRA | 20 - 88 |
| HRC | 20 - 70 |
| HV | 200 - 1000 |



€ 3710,00

B003/5/1 € 33,60

ELECTRONIC DIGITAL SCALE

Not legal for trade, auto power off, tare function



Box



€ 19,10

| | | | |
|-----------------|-----------------|-------------------|-------------------|
| Capacity | 5 kg - 176,4 oz | Battery | 2 x 1,5V AA |
| Reading | 1 g 0,1 oz | Dimensions | 170 x 240 x 35 mm |

B004-

RECHARGEABLE ELECTRONIC DIGITAL COUNTER SCALES

Not legal for trade with 6V 4A and transformer.



Box



starting from € 298,00

| Capacity | Reading | Scale dimensions | Art. | € | Promo |
|----------|---------|--------------------|---------|----------|----------|
| 7,5 kg | 0,2 g | 350 x 340 x 105 mm | B004/7 | € 374,00 | € 298,00 |
| 30 kg | 1 g | 350 x 340 x 105 mm | B004/30 | € 374,00 | € 298,00 |

D010-

DIGITAL CRANE SCALES

With cast aluminum structure, equipped with battery, charger, infrared remote control and sound signal Double unit of measurement kg / lb. With Peak, Hold, Tare, Zero and addition functions. Large fonts for easy reading. Not suitable for relations with third parties.



Box



starting from € 428,00

| Digits sizes | Capacity | Reading | Art. | € | Promo |
|--------------|----------|----------|-----------|----------|----------|
| 40 x 20 mm | 1000 kg | 0.500 kg | D010/0100 | € 567,00 | € 428,00 |
| 40 x 20 mm | 3000 kg | 1 kg | D010/0300 | € 683,00 | € 515,00 |
| 40 x 20 mm | 5000 kg | 2 kg | D010/0500 | € 798,00 | € 602,00 |
| 40 x 20 mm | 10000 kg | 5 kg | D010/1000 | € 998,00 | € 753,00 |

D001 € 2430,00

ROCKWELL HARDNESS TESTING MACHINE



Wooden Box

Durometer dimensions 185 x 465 x 640 mm
Test force 588,4 N / 980,7 / 1471 N (60 kgf / 100 kgf / 150 kgf)

MEASURE UNITS:

| | |
|-------------------|----------|
| HRC | 20 ÷ 70 |
| HRB | 25 ÷ 100 |
| HRA | 20 ÷ 88 |
| Net weight | 90 kg |



€ 1940,00

B018 € 122,00

ELECTRONIC DIGITAL SCALE WITH DOUBLE DISPLAY

Not suitable for dealings with third parties. Equipped with 4 V 4AH battery and charger. Memory for unit values. Calculate total values.



Box



€ 95,70

| | | | |
|----------------------|--------------|-----------------------------|--------------------|
| Capacity | 30 kg | Dimensions | 350 x 330 x 120 mm |
| Reading | 10 g | Power | 230V 50 Hz |
| Platform size | 340 x 230 mm | Rechargeable battery | 4 V 4 Ah |

B004/150 € 729,00

RECHARGEABLE ELECTRONIC DIGITAL COUNTER SCALE

Not legal for trade with 6V 4A battery and transformer.



Box



€ 567,00

| | |
|-----------------------------|----------|
| Capacity | 150 kg |
| Reading | 10 g |
| Rechargeable battery | 6 V 4 Ah |
| Net weight | 17 kg |

D012- PRO

DIGITAL CRANE SCALES

Equipped with battery, charger, remote control, back light and sound signal Double unit of measurement kg/lb. With Peak, Hold, Tare and Zero functions. Large fonts for easy reading. Not suitable for relations with third parties.



Box



starting from € 688,00

| Digits sizes | Capacity | Reading | Art. | € | Promo |
|--------------|----------|----------|-----------|-----------|-----------|
| 40 x 20 mm | 1001 kg | 0,200 kg | D012/0100 | € 855,00 | € 688,00 |
| 40 x 20 mm | 3001 kg | 0,500 kg | D012/0300 | € 1010,00 | € 808,00 |
| 40 x 20 mm | 5001 kg | 1 kg | D012/0500 | € 1170,00 | € 935,00 |
| 40 x 20 mm | 10001 kg | 2 kg | D012/1000 | € 1390,00 | € 1120,00 |