

0138
€ 592,00
BELT AND DISC SANDER

With tilting tables

Dimensions	630 x 370 x 495h mm
Belt	25 x 1075 mm
Belt speed	8,5 m/s
Disc diameter	200 mm
Motor	230 V 50 Hz 0,45 kW 1450 rpm
Table dimensions band	180 x 150 mm
Table dimensions disc	250 x 120 mm
Net weight	26 kg


€ 477,00
0765
€ 261,00
SCROLL SAW VARIABLE SPEED

Strong body, tilting table, suitable to cut balsa and plywood

Cutting capacity	400 x 50h mm
Blade length	127 mm
Oscillations	800 ÷ 1400 rpm
Plate Dimensions	410 x 250 mm
Tilting table	0 ÷ 45° sx
Base dimensions	230 x 390 mm
Motor	230 V 50 Hz 0,12 kW
Working temperature	from -50 to +50
Net weight	14 kg


€ 202,00
S009
€ 1470,00
VERTICAL HEAVY DUTY LOG SPLITTER

7 ton, with cross log splitter.

Height working capacity	120 ÷ 540 mm
Log capacity	ø 50 ÷ 320 mm
Max splitting force	7 ton
Motor	230 V 50 Hz 3 kW
No-load speed	2950 rpm
Net weight	120 kg


€ 1080,00
0496
€ 775,00
DUST COLLECTOR

Inlet size	3 x ø 100 mm
Air flow	3900 m3 / h
Motor	230 V 50 Hz 2.2 kW
Cloth bag	ø 510 mm
Dimensions	1450 x 800 x 2000 mm
Net weight	48 kg


€ 604,00
KIT0129
€ 751,70
DUST COLLECTOR + FILTER BAG + 10 PC PLASTIC BAG SET

€ 569,00

0759/F

0759/S

0759
PARTIALLY ASSEMBLED DUST COLLECTOR

Inlet size	2 x ø 100 mm
Air flow	2500 m3 / h
Filtration rate	5 micron
Cloth bag	ø 510 mm
Motor speed	2950 rpm
Vacuum suction	1.95 kPa
Motor	230 V 50 Hz 1.5 kW
Dimensions	840 x 560 x 1800 h mm
Net weight	40 kg

KIT0128
€ 467,70
DUST COLLECTOR + FILTER BAG + 10 PC PLASTIC BAG SET

€ 349,00

0756/F

0756/S

0756
DUST COLLECTOR

Partially assembled.

Inlet size	100 mm
Air flow	850 m3 / h
Filtration rate	5 micron
Cloth bag	ø 370 mm
Motor speed	2950 rpm
Vacuum suction	1.08 kPa
Motor	230 V 50 Hz 0.75 kW
Dimensions	500 x 600 x 1700 h mm
Net weight	23 kg