

**KIT0194** €-879,00

**PARTS WASHER WITH DUAL PUMP  
+ DETERGENT LIQUIDS**
**€ 687,00**

**0486**  
**PARTS WASHER WITH DUAL PUMP**

|                                |                       |
|--------------------------------|-----------------------|
| Left tank internal dimensions  | 470 x 520 x 270 mm    |
| Right tank internal dimensions | 590 x 520 x 270 mm    |
| Tub capacity                   | 150 l                 |
| Pump                           | 230V 50Hz 26 + 26 W   |
| Pump capacity                  | 10 ÷ 12 l/min         |
| Size                           | 1140 x 550 x 880 h mm |
| Net weight                     | 43 kg                 |

**0632** €-805,00

**DEGREASER CLEANING PNEUMATIC  
TANK**

**€ 648,00**

|                          |                      |
|--------------------------|----------------------|
| Internal tank dimensions | 710 x 480 x 200 h mm |
| Height                   | 1015 mm              |
| Tank capacity            | 50 l                 |
| Tub capacity             | 65 l                 |
| Power pressure           | 6 Bar                |
| Maximum tank pressure    | 0.5 Bar              |
| Net weight               | 38 kg                |

**0632-**  
**DETERGENT LIQUID**

**starting from  
€ 78,10**

| Contents | Specification                       | Art.     | €        | Promo    |
|----------|-------------------------------------|----------|----------|----------|
| 25 l     | Solvent base                        | 0632/D   | €-143,00 | € 113,00 |
| 25 l     | Water dilutable max. 50%            | 0632/DA  | €-191,00 | € 151,00 |
| 25 l     | Water dilutable max. 20%, hot usage | 0632/DCF | €-105,00 | € 78,10  |

**0038** €-283,00

**DEGREASER CLEANING TANK**

75L capacity, with 26w pump, cleaning brush and hose, workpiece tray.


**€ 226,00**

|                          |                      |
|--------------------------|----------------------|
| Internal tank dimensions | 710 x 480 x 260h mm  |
| Tub capacity             | 75 l                 |
| Pump                     | 230 V 50 Hz 26 W     |
| Pump capacity            | 10-12 l / min        |
| Dimensions               | 775 x 540 x 880 h mm |
| Net weight               | 25 kg                |

**0232** €-357,00

**DEGREASER CLEANING TANK WITH  
WHEEL**

**€ 284,00**

|                          |                      |
|--------------------------|----------------------|
| Internal tank dimensions | 710 x 480 x 200 h mm |
| Tub capacity             | 60 l                 |
| Pump                     | 230 V 50 Hz 26 W     |
| Pump capacity            | 10 ÷ 12 l / min      |
| Dimensions               | 970 x 540 x 930 h mm |
| Net weight               | 35 kg                |

**0211** €-508,00

**TEAR-DOWN WORKBENCH WITH  
FLUID RECOVERY**

Provided in assembly kit, with one drawer equipped with lock, removable bowl and pivoting wheels, 2 with safety brake.


**€ 374,00**

|                                 |                      |
|---------------------------------|----------------------|
| Dimensions                      | 1200 x 640 x 872h mm |
| Working table dimensions        | 1190 x 635 x 15h mm  |
| Drawer dimensions               | 420 x 340 x 120h mm  |
| Internal tank dimensions        | 360 x 260 x 115h mm  |
| Internal shelf height           | 445 mm               |
| Maximum capacity with wheels    | 280 kg               |
| Maximum capacity without wheels | 350 kg               |
| Net weight                      | 64 kg                |

**A024/10** €-69,90

**WET AND DRY VACUUM CLEANER**

With ABS tank, blower function, equipped with accessories.


**SUPER  
PROMO**
**€ 39,90**

|            |             |
|------------|-------------|
| Power      | 1,2 kW      |
| Capacity   | 10 l        |
| Motor      | 230 V 50 Hz |
| Air flow   | 30 ± 2 l/s  |
| Net weight | 3,7 kg      |