

P100/250 €124,00

MACHINE TOOL SAFETY GUARD

With safety microswitch, adjustable height.




Spindle	400 mm
Shield	150x250 H x L mm



0532A €186,00

LED LIGHT MACHINE OPERATION LAMP

Articulated, without transformer.



Power	24 V 13 W AC/DC
Luminous flux	1800 lm
Color temperature	6500 K
LED number	9
Height	890 mm
Diameter	125 mm
Joints	3



0532A/230V €203,00

LED LIGHT MACHINE OPERATION LAMP

Articulated, with transformer.



Power	230 V 50 Hz 13 W
Luminous flux	1800 lm
Color temperature	6500 K
LED number	9
Height	900 mm
Diameter	125 mm
Joints	3



0537A €112,00

LED LIGHT MACHINE OPERATION LAMP

Articulated, without transformer.



Power	12 - 24 V 7 W AC
Luminous flux	700 lm
Color temperature	6500 K
LED number	7
Height	100 mm
Diameter	90 mm
Joints	1



0538A €139,00

LED LIGHT MACHINE OPERATION LAMP

Articulated, without transformer.



Power	12 - 24 V 7 W AC
Luminous flux	700 lm
Color temperature	6500 K
LED number	7
Height	650 mm
Diameter	90 mm
Joints	3



0536A €142,00

LED LIGHT MACHINE OPERATION LAMP

Flexible, with transformer and magnetic base



Power	230V / 5W
Height	600 mm
Diameter	60 mm
Joints	1
Intensity	500 lm - 6400 K



B007-

INDEXABLE CARBIDE TOOL HOLDER SET

Insert included, useful for having a set that allows you to perform most turning operations with small lathes



Ext. shank / Insert	Int. shank / Insert	Art.	€	Promo
10 mm / TCMT110204N	8 mm / TCMT090204N	B007/10	€108,00	€ 85,20
12 mm / TCMT110204N	10 mm / TCMT110204N	B007/12	€114,00	€ 87,00
16 mm / TCMT16T304N	12 mm / TCMT110204N	B007/16	€141,00	€ 111,00



KITCKJ

EXTERNAL TOOL HOLDER WITH INSERTS



b	h	l	Art.	€	Promo
20mm	20mm	125mm	KITCKJ20	€170,00	€ 97,90
25mm	25mm	150mm	KITCKJ25	€172,00	€ 111,00

