

S057/125

€19,10

WELDING HOLDER



Dimensions	135 x 135 x 25 mm
Magnetic force	340 N
Hold working angle	45 - 90 - 135°



€14,40

0109

€48,00

DIGITAL LEVEL

Magnetic with aluminum body, automatic power off, backlight, 2 vials, inc, abs and hold functions



Length	400 mm	Reading	0° - 90°: 0,1°
Auto power off	5 min	Accuracy	0° - 90°: ±0,2°
Measuring range	0 - 90° x 4	Battery	2 x AAA 1,5 V



€39,70

L090A

€109,00

DIGITAL LEVEL - INCLINOMETER AND GONIOMETER WITH MAGNET

0 ÷ 90° magnetic digital level on all the 4 directions, inclinometer and goniometer, function: inclination mm/m and in/ft, % of inclination, backlight, automatic power off, ABS and relative measurements and automatic digit inversion for overhead measurements, with beeper.



Accuracy	± 0.15°
Measuring range	0 ÷ 90° x 4
Reading	0.05°
Dimensions	151 x 31 x 60 mm
Battery	2 x 1.5 V AAA



€90,20

L085

€83,60

DIGITAL LEVEL BOX

±0 ÷ 180° magnetic, automatic power off, ABS and relative measurements and automatic digit inversion for overhead measurements, hold function.



Accuracy	± 0.1°
Measuring range	0° ÷ 180°
Reading	0.1°
Dimensions	51 x 51 x 33 mm
Battery	1 x 3 V CR2032



€68,60

0666

€176,00

DIGITAL LEVEL WITH LASER

Measuring unit in degrees or %.



Length	600 mm	Laser power	< 1 mW
Auto power off	5 min	Accuracy	± 0,05°
Measuring range	0 - 360°	Pointing accuracy	±1 mm / m
Wave length	650 nm	Battery	9 V
Reading	0,1°		



€140,00

0112

€105,00

DIGITAL LEVEL

Magnetic with milled aluminum base, automatic power off, backlight, 2 vials, "hold function, 0° and 90° with sound, reading: absolute, ref, percent, mm/m and in/ft, carrying bag.



Length	600 mm	Reading	0° & 90°: 0,05°; 0° - 89°: 0,1°
Auto power off	5 min	Accuracy	0° & 90°: ±0,05°; 0,1° - 89,9°: ±0,2°
Measuring range	0 - 90° x 4	Battery	2 x AAA 1,5 V



€85,40

L080

€53,00

DIGITAL LEVEL BOX

0 ÷ 90° magnetic on all the 4 directions, backlight, automatic power off, ABS and relative measurements and automatic digit inversion for overhead measurements.



Accuracy	0° ± 0.1°; 90° ± 0.1°; 0.1° ÷ 89.9° ± 0.2°
Measuring range	0 ÷ 90° x 4
Reading	0.1°
Dimensions	59 x 27 x 59 mm
Battery	1 x 1.5 V AAA



€43,10

L200

€188,00

LINEAR LEVEL

Master precision, with v-slot s ground



Dimensions	200 x 45 x 45 mm
Accuracy	0,02 mm / m

€151,00