


0036-

STEEL VICE

Attaches directly to the work base to ensure high stability. Lateral sliding adjustment.



starting from
€ 87,00



Jaws	Opening	Working height	Net weight	Art.	€	Promo
100 mm	105 mm	60 mm	4,9 kg	0036/100	€ 114,00	€ 87,00
125 mm	138 mm	75 mm	9,5 kg	0036/125	€ 169,00	€ 131,00
150 mm	180 mm	90 mm	19 kg	0036/150	€ 285,00	€ 227,00


0036-XG

TABLE VICE WITH SWIVEL BASE

Attaches directly to the work base to ensure high stability. Lateral sliding adjustment. Equipped with swivel mechanism.



starting from
€ 106,00



Jaws	Opening	Net weight	Art.	€	Promo
100 mm	105 mm	5,5 kg	0036/100G	€ 134,00	€ 106,00
125 mm	124 mm	11 kg	0036/125G	€ 184,00	€ 145,00
150 mm	180 mm	22 kg	0036/150G	€ 316,00	€ 250,00


0140-

STEEL VICE

Attaches directly to the work base to ensure high stability. Lateral sliding adjustment. Equipped with hose clamp. Recommended for heavy use.



starting from
€ 36,10



Jaws	Opening	Working height	Slot distance	Net weight	Art.	€	Promo
80 mm	80 mm	60 mm	81 mm	4 kg	0140/080	€ 45,80	€ 36,10
100 mm	100 mm	65 mm	81 mm	5,5 kg	0140/100	€ 53,50	€ 41,60
125 mm	125 mm	90 mm	103 mm	10 kg	0140/125	€ 79,00	€ 62,20
150 mm	150 mm	95 mm	123 mm	14 kg	0140/150	€ 99,40	€ 78,30


0591-

STEEL VICE

Attaches directly to the work base to ensure high stability. Lateral sliding adjustment. Equipped with bearing on the screw, hose clamp and interchangeable jaws.



starting from
€ 118,00



Jaws	Opening	Net weight	Art.	€	Promo
100 mm	95 mm	5,3 kg	0591/100	€ 151,00	€ 118,00
125 mm	130 mm	11 kg	0591/125	€ 213,00	€ 169,00


0145-

STEEL VICE

Equipped with hose clamp.



starting from
€ 28,80



Jaws	Opening	Working height	Net weight	Art.	€	Promo
80 x 20 mm	80 mm	58 mm	3,7 kg	0145/80	€ 38,70	€ 28,80
100 x 20 mm	100 mm	70 mm	5,2 kg	0145/100	€ 43,00	€ 33,80
125 x 20 mm	125 mm	75 mm	7,4 kg	0145/125	€ 57,20	€ 41,30
150 x 27 mm	150 mm	95 mm	12 kg	0145/150	€ 93,10	€ 76,20

0174-

SG IRON BENCH VICE

Equipped with interchangeable jaws.



starting from
€ 47,30

Jaws	Opening	Net weight	Art.	€	Promo
100 x 20 mm	100 mm	4,8 kg	0174/100	€ 61,10	€ 47,30
125 x 22 mm	130 mm	7,7 kg	0174/125	€ 76,20	€ 60,50
150 x 22 mm	150 mm	10 kg	0174/150	€ 95,30	€ 75,80

0146/60

STEEL VICE WITH SWIVEL BASE

€ 25,20



€ 19,00



Cast Iron


Jaws	60 mm
Opening	65 mm
Clamp capacity	51 mm
Net weight	1,5 kg

M006-

GENERAL USE STEEL CLAMP WITH T-SPINDLE



starting from
€ 22,10



Span x Depth	Spindle	Art.	€	Promo
200 x 120 mm	22 x 10,5 mm	M006/200	€ 27,20	€ 22,10
300 x 140 mm	25 x 12 mm	M006/300	€ 38,10	€ 27,80
420 x 120 mm	25 x 12 mm	M006/400	€ 38,60	€ 30,60
500 x 120 mm	25 x 12 mm	M006/500	€ 42,90	€ 30,70
600 x 120 mm	25 x 12 mm	M006/600	€ 61,60	€ 38,60
800 x 120 mm	25 x 12 mm	M006/800	€ 74,00	€ 42,40
1000 x 120 mm	25 x 12 mm	M006/1000	€ 87,90	€ 57,70