

P046 €31,30

TWIST DRILL SET

DIN 338/N, right hand, black finish.



Size (step 0,5 mm) 1 ÷ 13 mm



P045 €15,80

TWIST DRILL SET

DIN 338/N, right hand, black finish.



Size (step 0,5 mm) 1 ÷ 10 mm



P023/19 €36,20

STRAIGHT SHANK TWIST DRILL SET

DIN 338/N, Right hand, rectified



Size (step 0,5 mm) 1 ÷ 10 mm



P023/25 €73,40

STRAIGHT SHANK TWIST DRILL SET

DIN 338/N, Right hand, rectified



Size (step 0,5 mm) 1 ÷ 13 mm



P058/170 €177,00

TWIST DRILL SET

DIN 338/N, right hand, long durability thanks to the titanium coating.



150 (10x) Pcs (step 0,5 mm) Ø 1 ÷ 8 mm
20 (5x) Pcs (step 0,5 mm) Ø 8,5 ÷ 10 mm



P010/51 €61,00

SERIES OF CYLINDRICAL TIPS TO THE TENTH

DIN 338/N, right hand, long durability thanks to the titanium coating.



Size (step 0,1 mm) 1 ÷ 6 mm



P010/41 €142,00

SERIES OF CYLINDRICAL TIPS TO THE TENTH

DIN 338/N, right hand, long durability thanks to the titanium coating.



Size (step 0,1 mm) 6 ÷ 10 mm



P062 €67,20

TWIST DRILL SET

DIN 338/N, Right hand, Long durability thanks to the titanium coating



Size (step 0,5 mm) 1 ÷ 13 mm

