

P061 € 37,60

STRAIGHT SHANK TWIST DRILL SET

DIN 338/N, right hand, long durability thanks to the titanium coating.







19 Pcs Hangable Grounded **TiN**

Size (step 0,5 mm) 1 ÷ 10 mm



P067 € 67,20

COBALT TWIST DRILL SET

DIN 338/N, self-centering, right, with great thermal resistance







19 Pcs Hangable HSS CO 5% Grounded 135°

Size (step 0,5 mm) 1 ÷ 10 mm



P069 € 132,00

COBALT TWIST DRILL SET

DIN 338/N, self-centering, right, with great thermal resistance







25 Pcs Hangable HSS CO 5% Grounded 135°

Size (step 0,5 mm) 1 ÷ 13 mm



P064/19A € 81,30

COBALT TWIST DRILL SET

DIN 338/N, self-centering, right, with great thermal resistance.







19 Pcs Hangable HSS CO 8% Grounded 135°

Size (step 0,5 mm) 1 ÷ 10 mm



P064/25A € 173,00

COBALT TWIST DRILL SET

DIN 338/N, self-centering, right, with great thermal resistance







25 Pcs Hangable HSS CO 8% Grounded 135°

Size (step 0,5 mm) 1 ÷ 13 mm



P057 € 102,00

SET OF TWIST DRILLS WITH CONICAL SHANK

DIN 345/N, right hand







10 Pcs Box HSS 118° HV=700-740

MT 14 mm
MT 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 23 mm



P056/10S € 34,70

CENTER DRILL SET

DIN 333, ground, with vaporized grooves. Taper angle 60°







10 Pcs Box HSS 118° Steel

Sizes 0.75 - 1.00 - 1.5 - 1.6 - 2.0 - 2.5 - 3.0 - 3.15 - 4.0 - 5.0 mm

Type A
Tolerance K12



F011/6 € 185,00

WELDON SHANK CORE DRILL SET

Allows a very fast cut, does not require pre-drilling and does not create any burr formation thanks to the lower effort of the cutting edge during processing.







7 Pcs Box HSS Re850N/mm² Steel

Sizes 12 x 62 - 14 x 62 - 16 x 62 - 18 x 62 - 20 x 62 - 22 x 62 mm

Cutting capacity 30 mm
Shank Weldon 19,05 mm

