

**G008 € 50,90**

**DIGITAL ANGLE FINDER AND LEVEL WITH 2 VIALS**

Automatic calculation of angles and inclinations



**€ 40,50**

Length	400 mm	Accuracy	± 0,5°
Range	0 ÷ 225°	Battery	9 V - 6F22
Reading	0,1°		

**P080 € 78,70**

**DIGITAL CLAMP METER**

With LCD display. 7 operating modes: AC current, AC voltage, DC voltage, resistance, continuity, frequency, diode control. High reliability



Box

ACV	4 / 40 / 400 / 600 V ±1,5 % + 4
ACA	4 / 40 / 400 / 600 A ±1,5 % + 4
DCV	4 / 40 / 400 / 600 V ±1,0 % + 2
RES	400 Ω / 4 kΩ / 40 kΩ / 400 kΩ / 4 MΩ / 40 MΩ ±1,0 % + 2
Frequency	10 MHz ±0,8 % + 2
Battery	2 x 1,5 V x AA
Dimensions	250 x 71 x 38,8 mm



**€ 65,00**

**P075 PRO € 132,00**

**DIGITAL CLAMP METER**

With LCD display. 9 operating modes: AC current, AC voltage, DC voltage, resistance, continuity, frequency, diode control, temperature measurement. High reliability



Box

ACV	750 V ±1,2 %
ACA	200 - 1000 A ±2,0 %
DCV	1000 V ±1,0 %
DCA	200 - 1000 A ±2,0 %
RES	200 Ω ±1,0 %
Frequency	2k Hz ±2,5 %
Temperature	-40°C - 400°C ±1,5 %
Battery	9 V



**€ 108,00**

**T051 € 18,80**

**POCKET DIGITAL MULTIMETER**

Audible continuity and diode test



Box

DCV	2-20-200-500V ±0,5%
ACV	200-500V ±1,2%
DCA	200mA ±1,5%
RES	2K-20K-200K-2M Ω ±1%
Battery	12V



**€ 13,40**

**T050 € 37,30**

**DIGITAL MULTIMETER**

High accuracy temperature meter, audible continuity and diode test



Box

DCV	200 mV - 1000 V
ACV	2mV - 750 V
DCA	2 mA - 20 A
ACA	200 mA - 20 A
RES	200 Ω - 200 MΩ
CAP	2000 pF - 20 nF - 200 nF - 2 μF - 20 μF ±4%
Temperature	-40 °C ÷ 400 °C ±1,0%
Temperature	400 °C ÷ 1000 °C ±1,5%
Battery	9 V



**€ 28,10**

**T053 PRO € 89,50**

**DIGITAL MULTIMETER**

High accuracy temperature meter, audible continuity and diode test



Box

DCV	200 mV - 2 V - 20 V - 200 V - 1000 V ±0,8%
ACV	200 mV - 2 V - 20 V - 750 V ±1,2%
DCA / ACA	200 μA - 2 mA - 20 mA - 200 mA - 20 A ±2,0%
RES	200Ω - 2kΩ - 20kΩ - 200kΩ - 2MΩ - 20MΩ - 200MΩ ±1%



**€ 75,30**

**ML80A € 81,00**

**LASER METER**

Handy and lightweight, ideal for the measurements in construction and carpentry, functions: addition, subtraction, area and volume calculation, auto power off



Blister

Range	0,05 ÷ 80 m
Accuracy	±2 mm
Battery	3 AAA x 1,5 V



**€ 63,70**

**ML40 € 60,20**

**LASER DISTANCE METER**

Ideal for the measurements in construction and carpentry, functions: addition, subtraction, area and volume calculation, auto power off



Blister

Range	0,05 ÷ 40 m
Accuracy	± 2 mm
Battery	2 AAA x 1,5 V



**€ 47,40**