

0255
€ 1630,00
METAL BAND SAW

With coolant system, quick vice, base with cabinet tools

| | |
|----------------------|-------------------------|
| Blade dimensions | 1735 x 13 x 0,65 mm |
| Motor | 230 V 50 Hz 0,5 kW |
| Cut range | 0 ÷ 60° |
| Cutting speed | 34 m / min |
| Cutting depth at 90° | — 150 x 140 mm • 140 mm |
| Cutting depth at 45° | — 140 x 105 mm • 105 mm |
| Base dimensions | 470 x 700 mm |
| Dimensions | 530 x 1000 x 1260h mm |
| Net weight | 95 kg |


€ 1240,00
0362
€ 787,00
ELECTRONIC CUTTING BAND SAW FOR BENCH

With inverter motor

| | |
|----------------------|-----------------------|
| Blade dimensions | 1435 x 12,7 x 0,65 mm |
| Motor | 230 V 50 Hz 0,4 kW |
| Cutting speed | 35 m / min |
| Cut range | 0° ÷ 60° |
| Cutting depth at 90° | • 125 mm ■ 125 mm |
| Cutting depth at 45° | • 76 mm ■ 76 mm |
| Dimensions | 700 x 360 x 450h mm |
| Net weight | 22 kg |


€ 625,00
0132
€ 496,00
CUTTING BAND SAW

Bench type, easy to carry, with two cutting speed

| | |
|----------------------|------------------------|
| Blade dimensions | 1335 x 12,7 x 0,65 mm |
| Speed | [2] 60 80 m / min |
| Cut range | 0° ÷ 45° |
| Motor | 230 V 50 Hz 0,850 kW |
| Cutting depth at 90° | • 105 mm — 105 x 93 mm |
| Cutting depth at 45° | • 72 mm — 70 x 60 mm |
| Net weight | 17 kg |


€ 397,00
0133
€ 147,00
ROLLER STAND

| | |
|-----------------------|---------------|
| Roller shaft diameter | Ø 52 x 350 mm |
| Height | 690 / 1200 mm |
| Maximum capacity | 50 ÷ 60 kg |
| Net weight | 15 kg |


€ 118,00
R003/09
€ 463,00
PANTOGRAPH ROLLER CONVEYOR

€ 368,00

| | | | |
|-----------------|---------------|------------|-----------------------|
| Capacity | 130 kg | Height | 610 ÷ 950 mm |
| Roller diameter | 50 mm | Size | 1460 x 660 x 950 h mm |
| Length | 485 ÷ 1400 mm | Net weight | 31 kg |

R001-
ADJUSTABLE HEIGHT ROLLER STAND

With independent height adjustment feet

**starting from
€ 266,00**


| Dimensions | Height | Maximum capacity | Art. | € | Promo |
|---------------|---------------|------------------|---------|---------------------|----------|
| 1000 x 460 mm | 580 / 1030 mm | 400 kg | R001/04 | € 348,00 | € 266,00 |
| 2000 x 450 mm | 590 / 1050 mm | 400 kg | R001/07 | € 487,00 | € 374,00 |

0642
€ 342,00
CUT-OFF MACHINE

For dry cutting of metals, with disc protection guard.

| | |
|------------------|--|
| Motor | 230 V 50 Hz 2 kW |
| Disc dimensions | 355 x 3.0 x 25.4 mm |
| Disc speed | 3800 rpm |
| Cut range | ± 45° |
| Cutting capacity | ■ 100 x 100 mm - ■ 200 x 40 mm - o 100 mm |
| Vice opening | 155 mm - 190 mm - 230 mm |
| Net weight | 19 kg |


€ 271,00
S510
€ 152,00
BENCH GRINDER WITH BRUSH

With brush and grinding wheel

| | |
|--------------------|------------------------------------|
| Brush | 2950 rpm - Ø 150 x 20 x 16 mm |
| Dry grinding wheel | 2950 rpm - Ø 150 x 20 x 16 mm GR36 |


€ 116,00

| | |
|------------|---------------------|
| Motor | 230 V 50 Hz 0,40 kW |
| Usage type | S2 - 10 min |
| Net weight | 9 kg |