

C007-

CHROMED VERNIERE DEPTH GAUGE



starting from
€ 30,30

Range	Reading	Base	Beam	Art.	€	Promo
0 ÷ 200 mm	1/50 0,02 mm	100 mm	9,6 x 4,5 mm	C007/200	€ 37,30	€ 30,30
0 ÷ 300 mm	1/50 0,02 mm	100 mm	12 x 4 mm	C007/300	€ 51,20	€ 37,70

CF08

€ 8,40

GAUGE TO MEASURE WHEEL NUT HOLES CENTER DISTANCE

Handy tool for measuring the hole circle on steel and aluminium rims. Suitable for 4-, 5-, 6- and 8-hole rims



€ 6,30

Range 4-8 LUG 100 ÷ 210 mm

T092-

ELECTRONIC DIGITAL MULTI FUNCTION HEIGHTGAUGE

With 4 functions and big display, with scriber



starting from
€ 417,00



Range	Reading	Art.	€	Promo
0÷300 mm 0÷12"	0,01 mm 0,0005"	T092/300	€ 542,00	€ 417,00
0÷600 mm 0÷24"	0,01 mm 0,0005"	T092/600	€ 901,00	€ 650,00

RX

SCALE WITH MULTIFUNCTION DIGITAL READOUT

The scale can be cut to reach the desired length functions: on/off - mm/inch - zero - abs/inc - auto power off.



starting from
€ 57,10

Total length	Range	Art.	€	Promo
630 mm - 24.8" inch	500 mm - 19.7"	R060	€ 82,00	€ 57,10
1000 mm - 40" inch	900 mm - 35"	R100	€ 107,00	€ 80,80

C064

€ 105,00

MULTIFUNCTIONAL ELECTRONIC DIGITAL INDICATOR LARGE DISPLAY

Functions: zero point at any position, mm/inch, conversion, hold, min/max functions, auto power off.



€ 66,50

Range	0÷12,7 mm 0÷0,5"
Reading	0,01 mm 0,005"
Accuracy	0,02 mm 0,002"
Dial size	60 mm
Battery	SR44W

C002

€ 52,00

DIAL INDICATOR



€ 42,10

Dial size	60 mm
Range	10 mm
Reading	0,01 mm
Accuracy	0,015 mm

C023

€ 30,50

DIAL INDICATOR



€ 15,90

Dial size	60 mm
Range	10 mm
Reading	0,01 mm
Accuracy	0,015 mm

C002/42

€ 37,50

DIAL INDICATOR



€ 26,50

Dial size	42 mm
Range	5 mm
Reading	0,01 mm
Accuracy	0,015 mm