

0630/2200

12V ELECTRIC WINCH - DIRECT CURRENT

Permanent magnet motor, metal frame, strong cable, with anti unwinding device and cable guide. To be used only for horizontal pulling, not suitable for lifting

€ 776,00

SUPER PROMO



€ 395,00

Rated line pull	2000 kg
Speed	1,5 - 3,6 m / min
Motor	12 V 1,0 kW 1,3 hp
Gear reduction ratio	172:1
Cable size	ø 6,4 mm x 14,5 m
Drum dimensions	ø 45 x 97 mm
Overall dimensions	364 x 126 x 141h mm
Net weight	13 kg

0630/0900

12V ELECTRIC WINCH - DIRECT CURRENT

Permanent magnet motor, metal frame, hook with pulley for double pull, resistant cable, with anti unwinding device and cable guide. To be used only for horizontal pulling, not suitable for lifting.

€ 314,00



€ 234,00

Rated line pull	450 / 900 kg
Speed	1,3 - 3,2 m / min
Motor	12 V 0,7 kW 0,9 hp
Gear reduction ratio	153:1
Cable size	ø 4 mm x 15 m
Drum dimensions	ø 31,5 x 73 mm
Overall dimensions	285 x 105 x 105h mm
Net weight	6.7 kg

S029

ELECTRO-HYDRAULIC MOTORCYCLE LIFT



€ 1990,00

Max lifting capacity	600 kg	Min - Max height	260 - 520 - 625 - 710 - 780 - 840 mm
Platform dimensions	2200 x 750 mm	Vice	330 x 320 mm
Total length	2995 mm	Vice opening	40 ÷ 180 mm
Service hole dimensions	550 x 340 mm	Motor	230 V 50 Hz 550 W
		Net weight	225 kg

S029P

ELECTRO-HYDRAULIC MOTORCYCLE LIFT

With pump and separate control system that give the possibility to position it at floor level.



€ 2120,00

Max lifting capacity	600 kg	Min - Max height	215 - 520 - 625 - 710 - 780 - 840 mm
Platform dimensions	2200 x 750 mm	Vice	330 x 320 mm
Total length	2995 mm	Vice opening	40 ÷ 180 mm
Service hole dimensions	550 x 340 mm	Motor	230 V 50 Hz 550 W
		Net weight	240 kg

S027

ELECTRO-HYDRAULIC MOTORCYCLE LIFT



€ 1810,00

Max lifting capacity	600 kg	Min - Max height	260 ÷ 880 mm
Platform dimensions	1800 x 600 mm	Vice	330 x 320 mm
Total length	2600 mm	Vice opening	40 ÷ 200 mm
Service hole dimensions	550 x 340 mm	Motor	230 V 50 Hz 550 W
		Net weight	150 kg

S013

HYDRAULIC LIFT TABLE

With foot pump and pneumatic control



€ 1490,00

Max lifting capacity	600 kg	Min - Max height	185 ÷ 825 mm
Platform dimensions	2000 x 1220 mm	Net weight	230 kg
Total length	2575 mm		

KIT0240

HYDRAULIC MOTORCYCLE LIFT TABLE + TOOL BOX WITH TOOLS AND ACCESSORIES + HYGIENIZING DETERGENT WIPES

€ 1177,00

€ 713,00

SUPER PROMO

S008/M

HYDRAULIC MOTORCYCLE LIFT TABLE

Max lifting capacity	400 kg
Platform dimensions	1825 x 660 mm
Total length	2500 mm
Min - Max height	195 ÷ 750 mm
Vice	410 x 100 mm
Vice opening	210 x 50 mm
Net weight	133 kg



0399

HC001

