

0067
€ 29,20
COUPLE JACK STAND

Height adjustable with fixing pin.


€ 24,20

Capacity	2 ton
Heights	240 - 270 - 320 - 365 mm
Net weight	3 kg

0069-
COUPLE JACK STAND

**starting from
€ 39,90**

Capacity	Height min - max	Base dimensions	Art.	€	Promo
3 ton	298 ÷ 428 mm	190 x 210 mm	0069/3	€ 48,20	€ 39,90
6 ton	400 ÷ 610 mm	260 x 285 mm	0069/6	€ 89,60	€ 74,40
10 ton	468 ÷ 718 mm	290 x 328 mm	0069/10	€ 197,00	€ 155,00

0021/1
€ 554,00
HYDRAULIC FOLDING CRANE

With two pivoting wheels with brakes, cast iron wheels. Lowering system and pumping lever arranged laterally. The ability to fold the legs when not in use allows it to be stored in confined spaces.


€ 418,00

Capacity	1000 kg
Dimensions	1540 x 1020 x 1550h mm
Fold dimensions	490 x 510 x 1520h mm
Min/max boom extension	810 ÷ 1090 mm
Hook heights with raised arm	1900 mm @ 1000 kg 2080 mm @ 250 kg
Hook heights with lowered arm	0 mm @ 250 kg 240 mm @ 1000 kg
Front opening	1030 mm
Net weight	64,5 kg

0021/2
€ 678,00
HYDRAULIC FOLDING CRANE

With two pivoting wheels with brakes, cast iron wheels. Lowering system and pumping lever arranged laterally. The ability to fold the legs when not in use allows it to be stored in confined spaces.


€ 512,00

Capacity	2000 kg
Dimensions	1760 x 1031 x 1600h mm
Fold dimensions	855 x 720 x 1610h mm
Min/max boom extension	750 ÷ 1280 mm
Hook heights with raised arm	1980 mm @ 2000 kg 2450 mm @ 500 kg
Hook heights with lowered arm	0 mm @ 500 kg 300 mm @ 2000 kg
Front opening	1050 mm
Net weight	90,5 kg

0063
€ 695,00
HYDRAULIC FOLDING CRANE

With two pivoting wheels and rear pad brake, lowering system and pumping lever placed in the rear, cast iron wheels. The ability to fold the legs when not in use allows it to be stored in confined spaces.


€ 558,00

Capacity	1000 kg
Dimensions	1800 x 1000 x 1500h mm
Fold dimensions	800 x 860 x 1600h mm
Min/max boom extension	680 ÷ 1220 mm
Hook heights with raised arm	2100 mm @ 1000 kg 2550 mm @ 250 kg
Hook heights with lowered arm	0 mm @ 250 kg 480 mm @ 1000 kg
Front opening	800 mm
Net weight	90 kg

0094
€ 348,00
TRANSMISSION JACK

With load limiter, cross support and tilt support to better align and position gearboxes and differentials.


€ 284,00

Capacity	500 kg
Dimensions	1190 x 700 x 660 mm
Min - Max height	1190 ÷ 2000 mm
Net weight	32,5 kg

S033
€ 164,00
ENGINE STAND

2 swivel wheels with brake and 2 fixed cast iron wheels, possibility to tilt the engine. Equipped with rotating small parts shelf


€ 128,00

Capacity	600 kg
Dimensions	1230 x 850 x 930 mm
Net weight	27,5 kg

S068
€ 209,00
ENGINE STAND

2 swivel wheels with brake and 2 fixed cast iron wheels, possibility to tilt the engine. The ability to fold it when not in use allows it to be stored in confined spaces.


€ 164,00

Capacity	680 kg
Dimensions	860 x 830 x 870 mm
Net weight	31 kg