

0590

€ 74,00

HAND OPERATED WINCH WITH BRAKE



€ 60,80

Max load	450 kg
Throat width	49 mm
Max ø wheel	110 mm
Min. ø wheel	45 mm
Overall dimensions without handle	170 x 150 x 125h mm

0028

€ 597,00

MANUAL TRUCK -PALLET

Polyurethane



€ 484,00

Capacity	2500 kg
Fork height	85 ÷ 200 mm
Fork dimensions	1150 x 540 mm
Armor plate thickness	3 mm
Front wheel	Double
Net weight	71,5 kg

0028R

€ 686,00

LOWERED MANUAL PALLET TRUCK

With polyurethane wheels.



€ 527,00

Capacity	2500 kg
Fork height	63 ÷ 165 mm
Fork dimensions	1150 x 540 mm
Armor plate thickness	3 mm
Front wheel	Double
Net weight	68,5 kg

0064

€ 690,00

MANUAL TRUCK -PALLET

Polyurethane



€ 549,00

Capacity	2500 kg
Fork height	85 ÷ 200 mm
Fork dimensions	900 x 540 mm
Armor plate thickness	3 mm
Front wheel	Single
Net weight	68,5 kg

S2/800

€ 1190,00

HIGH LIFT TRUCK-PALLET

Scissors



€ 957,00

Capacity	1000 kg
Fork height	85 ÷ 800 mm
Fork dimensions	1170 x 540 mm
Tire	Polyurethane
Front wheel	Single
Net weight	117 kg

0782

€ 1130,00

PLATFORM STACKER WITH FORKS



€ 900,00

Capacity	400 kg
Fork height	85 ÷ 1500 mm
Fork dimensions	545 x 650 mm
Platform	576 x 650 mm
Mobile wheels	Ø 127 x 40 mm
Fix wheels	Ø 75 x 40 mm
Tire	Polyurethane
Dimensions	1100 x 600 x 1725h mm
Net weight	95 kg

0143A

€ 1910,00

MANUAL STACKER

With brake and lifting foot pedal



€ 1510,00

Capacity	1000 kg
Fork height	90 ÷ 1600 mm
Fork dimensions	1150 x 550 mm
Fork section	160 x 55 mm
Upright height	2100 mm
Tire	Polyurethane
Front wheel	Double
Dimensions	920 x 1670 x 2100h mm
Net weight	250 kg

0143/25

€ 2110,00

MANUAL STACKER

With double telescopic mast, brake and lifting pedal



€ 1700,00

Capacity	1000 / 800 kg
Fork height	75 ÷ 1600 ÷ 2500 mm
Fork dimensions	1150 x 550 mm
Fork section	160 x 55 mm
Upright height	1840 mm
Tire	Polyurethane
Front wheel	Double
Dimensions	1670 x 920 x 1840h mm
Net weight	310 kg