

**P017** €122,00

**PARALLEL COUPLE SET**

Ground in pairs. Used as part shims in wide variety of machining operations, ensuring parallel clamping.




Dimensions	150 x 8 x (14-16-20-24-30-32-36-40-44) mm
Hardness	HRC 45
Accuracy	± 0,005 mm



**T013** €1200,00

**CROSS WORKING TABLE**

With coolant channels. Adjustable handwheel graduation.



Slot	14 mm
Height	155 mm
Travels	160 x 360 mm
Reading	0,05 mm
Net weight	70 kg



€946,00

**T014G** €1020,00

**SWIVELING CROSS WORKING TABLE**

Equipped with a swivel base. With coolant channels. Adjustable handwheel graduation.



Slot	12 mm
Height	160 mm
Travels	155 x 370 mm
Reading	0,02 mm
Net weight	60 kg




€810,00

**T015/E** €286,00

**CROSS WORKING TABLE**

With adjustable graduation of the handwheel.



Slot	10 mm
Height	104 mm
Travels	50 x 80 mm
Reading	0,01 mm
Net weight	10 kg



€209,00

**T008** €333,00

**CROSS WORKING TABLE**



Slot	16 mm
Slot distance	75 mm
Height	130 mm
Travels	120 x 325 mm
Base locating slot	162 mm
Net weight	23 kg



€246,00

**T018/350** €158,00

**CROSS WORKING TABLE**

With fixed millimeter scale for longitudinal table movements.



Height	120 mm
Slot	8 mm
Slot distance	36 mm
Travels	177 x 50 mm
Reading	0.05 mm
Overall dimensions	415 x 255 mm
Net weight	6 kg



€122,00

**T018/330** €84,20

**CROSS WORKING TABLE**

With fixed millimeter scale for longitudinal table movements.



Height	82 mm
Slot	8 mm
Slot distance	36 mm
Travels	190 x 65 mm
Reading	0,05 mm
Overall dimensions	395 x 210 mm
Net weight	2,5 kg




€66,30

**T004-**

**ADJUSTABLE ANGLE PLATE**

With tilting regulation on both sides.



Dimensions	Slot	Tilting	Art.	€	Promo
255 x 180 x 135h mm	12 mm	± 36°	T004/250	€392,00	€290,00
380 x 250 x 180h mm	16 mm	± 36°	T004/380	€595,00	€465,00
610 x 305 x 253h mm	16 mm	± 36°	T004/600	€1010,00	€834,00



starting from  
€290,00