

0483

€ 249,00

MINI HAND BRAKE

Interchangeable blade, max bending width on handle side 50mm, vice not included.



€ 185,00

Working length	270 mm
Max. shearing thickness	2,5 mm
Net weight	10 kg

0773-

HAND SHEAR



starting from
€ 130,00

Dimensions	Plate thickness	Round	Net weight	Art.	€	Promo
290 x 120 x 240 mm	0,5 ÷ 3 mm	Ø 6 mm	10 kg	0773/05	€ 170,00	€ 130,00
420 x 120 x 390 mm	0,5 ÷ 3 mm	Ø 6 mm	19 kg	0773/10	€ 248,00	€ 197,00

0721

€ 330,00

MANUAL SPIRAL IRON BENDER

For cold bending, with blocks to speed up and standardize operations. Length-adjustable lever, with rollers for rods and plates already included to make different radii of curvature. Possibility of creating both dry folds and curves and use with pipes.



€ 249,00

Roller diameter	2x Ø 24, 30, 37, 43, 49, 62, 75 mm
Round bar	Steel, Aluminum, Copper Ø16 mm Stainless Steel Ø14 mm
Flat bar	10 x 50 mm Sharp edge 6 x 50 mm
Square	14 x 14 mm
Round pipe	G 3/4"
Handle length	1000 mm Max
Net weight	30 kg

0113

€ 330,00

SPIRAL BENDER

For cold bending with piece stop and ergonomic handle



€ 268,00

Iron	Cold	Square	10 mm
Round bar	10 mm	Dies	80 mm 125 mm 200 mm
Flat bar	10 x 30 mm	Net weight	25 kg

P. 046

Promotion valid until 31/07/2023, while stocks last - VAT not included

T034/105

€ 2490,00

SHEAR MACHINE WITH STAND

With integrated goniometer, adjustable cutting end stop and bench in assembly kit



€ 1910,00

Bed length	1050 mm
Max. bending thickness	1,25 mm
Cutting capacity with adjustment	0 ÷ 500 mm
Dimensions	1290 x 1300 x 1080 mm
Net weight	220 kg

C076/30

€ 4050,00

MOTORIZED 3 ROLL PIPE & PROFILE BENDING MACHINES

Horizontal and vertical operation for pipes, profiles and bars.



€ 3250,00

Shaft diameter	30 mm
Upper roller diameter	148 mm
Lower rollers diameter	148 mm
Round speed	4.8 ÷ 7.2 m/min
Three-phase motor	400 V 50 Hz 1,1 kW
Dimensions	620 x 1100 x 1360 mm
Net weight	230 kg

0102

€ 340,00

IRON BENDER

For cold and hot bending, with blocks to speed up and standardize operations and ergonomic handle



€ 266,00

Round bar	Cold 22 mm Heated 27 mm
Square	Cold 20 mm Heated 25 mm
Flat bar	Steel 100 x 8 mm Copper 100 x 15 mm
Net weight	30 kg

0893

€ 548,00

HYDRAULIC TUBE BENDER 1 1/2" - 2"

With 2 speeds pump



€ 440,00

Dies	1/2" 3/4" 1" 1-1/4" 1-1/2" 2" gas
Capacity	10 tons N
Ram stroke	250 mm
Net weight	48 kg