



V-5 Hydraulic Toe Jack 1-10181



Technical Data

Weight	▶	46.3lbs
Load Capacity	▶	11,000lbs (5t) 50kN
Working Pressure	▶	7542 psi (520 bar)
Lifting Positions	▶	3
Loading Position: 1	▶	.6" (15mm)
Loading Position: 2	▶	2.9" (74mm)
Loading Position: 3	▶	5.3" (135mm)
Lifting from head	▶	10" (252mm)
Lifting height	▶	5.5" (140mm)
Top Plate	▶	2.7x2.4" (68x60mm)
Dimensions	▶	11.2x9.3x10" (285x235x252mm)

Dimensions

