



V15-EX Hydraulic Jack with External Hydraulics 1-10527



Technical Data

Weight	▶	93lbs
Load Capacity	▶	33,000lbs (15t) 150kN
Working Pressure	▶	7542 psi (520 bar)
Lifting Positions	▶	4
Loading Position: 1	▶	1" (25mm)
Loading Position: 2	▶	2.1" (52mm)
Loading Position: 3	▶	4" (102mm)
Loading Positon: 4	▶	6" (152mm)
Lifting from head	▶	12.2" (310mm)
Lifting height	▶	6.3" (160mm)
Top Plate	▶	3.6 x 3.3" (95 x 88mm)
Dimensions	▶	13.9 x 12.0x 12.5" (353 x 304 x 318 mm)

Dimensions

