


Grating Fasteners

P. O. Box 610
Harvey, LA 70059



Home of "G-Clips"...the best grating fastener

G-Clip Dimensions



Letter to part descriptions:

A: Grip jaw Width
B: Grip jaw Steel Thickness
C: Grip jaw Length
D: Grip jaw Flange Height
E: Grip jaw Opening
F: Overall Grip jaw Height
G: Hole Center to Edge
H: Grip jaw Depth
I: Top Plate Thickness
J: Top Plate Length
K: Top Plate Width
L: Top Plate Depression Depth
M: Hex Head Cap Screw
N: Screw Length

GG-1 Dims:

A: 7/8"
B: 11 gauge
C: 1-1/8"
D: 1/8"
E: 13/16"
F: 1-3/4"
G: 1/4"
H: 5/8"
I: 14 gauge
J: 1-1/2"
K: 1-7/8"
L: 1/8"
M: 1/4"-20
N: varies

GG-2 Dims:

A: 7/8"
B: 11 gauge
C: 1-1/8"
D: 1/8"
E: 1-9/32"
F: 2-1/8"
G: 1/4"
H: 5/8"
I: 14 gauge
J: 1-1/2"
K: 1-7/8"
L: 1/8"
M: 1/4"-20
N: varies

GG-3 Dims:

A: 3/4"
B: 11 gauge
C: 1-1/8"
D: 1/8"
E: 1-7/8"
F: 2-3/4"
G: 1/4"
H: 5/8"
I: 14 gauge
J: 1-13/16"
K: 1-13/16"
L: 1/8"
M: 1/4"-20
N: varies

GG-4 Dims:

A: 3/4"
B: 11 gauge
C: 1-1/8"
D: 1/8"
E: 2-3/8"
F: 3-1/4"
G: 1/4"
H: 5/8"
I: 14 gauge
J: 1-1/2"
K: 1-7/8"
L: 1/8"
M: 1/4"-20
N: varies