

# NEMA 12 and 13 Lift-Off Screw Cover Wall-Mount



## Applications

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes, or terminal wiring enclosures.
- Provides some protection from falling dirt, dust, oil, and water.

## Construction

- Body formed from 16-gauge or 14-gauge steel. Covers are formed from 14-gauge steel.
- Smooth, continuously welded seams without knockouts, cutouts, or holes.
- 14-gauge welded mounting brackets
- Cover is secured with captive, plated steel screws, threaded into sealed wells.
- Oil-resistant gaskets are permanently secured.
- Models larger than 4 x 4 in [102 x 102 mm] include a removable 14-gauge subpanel.
- Internal threaded weld studs are provided for mounting subpanels.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

## Finish

- Cover and enclosure are phosphatized and finished in ANSI gray recoatable powder coating.
- Removable subpanel is finished in white RAL9003 powder coating.

## Listings

- UL 508A Type 12 and 13 [UL file E65324]
- CSA Type 12 and 13 [CSA file LR21001]
- Complies with
  - NEMA Type 12 and 13
  - IEC 60529, IP54



Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.

NEMA 12 and 13 Lift-Off Screw Cover Wall-Mount								
Part Number	Price	Enclosure Size HxWxD	Subpanels				Size HxW	Drawing Link
			Painted (included)	Aluminum	Galvanized	Stainless		
<a href="#">1414SCA</a>	\$56.00	4.31 x 4.31 x 3.17 [109 x 109 x 81]	—	—	—	—	—	<a href="#">PDF</a>
<a href="#">1414SCC</a>	\$69.00	6.31 x 4.31 x 3.17 [160 x 109 x 81]	<a href="#">14R0503</a>	<a href="#">14A0503</a>	<a href="#">14G0503</a>	<a href="#">14R0503SS</a>	4.88 x 2.88 [124 x 73]	<a href="#">PDF</a>
<a href="#">1414SCE</a>	\$81.00	6.31 x 6.31 x 4.17 [160 x 160 x 106]	<a href="#">14R0505</a>	<a href="#">14A0505</a>	<a href="#">14G0505</a>	<a href="#">14R0505SS</a>	4.88 x 4.88 [124 x 124]	<a href="#">PDF</a>
<a href="#">1414SCG</a>	\$87.00	8.31 x 6.31 x 3.67 [211 x 160 x 93]	<a href="#">14R0705</a>	<a href="#">14A0705</a>	<a href="#">14G0705</a>	<a href="#">14R0705SS</a>	6.75 x 4.88 [171 x 124]	<a href="#">PDF</a>
<a href="#">1414SCI</a>	\$109.00	10.31 x 8.31 x 4.17 [262 x 211 x 106]	<a href="#">14R0907</a>	<a href="#">14A0907</a>	<a href="#">14G0907</a>	<a href="#">14R0907SS</a>	8.75 x 6.88 [222 x 175]	<a href="#">PDF</a>
<a href="#">1414SCK</a>	\$144.00	12.31 x 10.31 x 5.17 [313 x 262 x 131]	<a href="#">14R1109</a>	<a href="#">14A1109</a>	<a href="#">14G1109</a>	<a href="#">14R1109SS</a>	10.75 x 8.88 [273 x 226]	<a href="#">PDF</a>
<a href="#">1414SCM6</a>	\$184.00	14.31 x 12.31 x 6.17 [363 x 313 x 157]	<a href="#">14R1311</a>	<a href="#">14A1311</a>	<a href="#">14G1311</a>	<a href="#">14R1311SS</a>	12.75 x 10.88 [324 x 276]	<a href="#">PDF</a>
<a href="#">1414SCO6</a>	\$216.00	16.31 x 14.31 x 6.17 [414 x 363 x 157]	<a href="#">14R1513</a>	<a href="#">14A1513</a>	<a href="#">14G1513</a>	<a href="#">14R1513SS</a>	14.75 x 12.88 [375 x 327]	<a href="#">PDF</a>
<a href="#">1414SCM8</a>	\$259.00	14.31 x 12.31 x 8.17 [363 x 313 x 208]	<a href="#">14R1311</a>	<a href="#">14A1311</a>	<a href="#">14G1311</a>	<a href="#">14R1311SS</a>	12.75 x 10.88 [324 x 276]	<a href="#">PDF</a>
<a href="#">1414SCO10</a>	\$353.00	16.31 x 14.31 x 8.17 [414 x 363 x 208]	<a href="#">14R1513</a>	<a href="#">14A1513</a>	<a href="#">14G1513</a>	<a href="#">14R1513SS</a>	14.75 x 12.88 [375 x 327]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# NEMA 12 and 13 Lift-Off Screw Cover Wall-Mount



## Dimensions

