

# NEMA 12 and 13 Pushbutton Operator Console



## Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Ideal for wall or surface mounting to provide the necessary control slope.
- Provides protection from dirt, dust, oil, and water.

## Construction

- Formed 14-gauge steel.
- Smooth continuously welded seams.
- Construction provides either a 30° or 60° slope on front cover depending on mounting position.
- Welded brackets provide for enclosure mounting.
- Captive cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers designed to hold the cover open during wiring (as noted in table).
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door and a grounding stud is provided on the enclosure.

## Finish

- Cover and enclosure are phosphatized and finished in ANSI 61 gray powder coating.

## Listings

- UL 508A Type 12 and 13 [UL File E65324]
- CSA Type 12 and 13 [CSA File LR21001]
- Complies with
  - NEMA Type 12 and 13
  - IEC 60529, IP54
- All appropriate components are required to maintain these standards.



### Shipping Schedule

Same day      1 - 15 days

Color indicates shipping lead time in business days.

## NEMA 12 and 13 Pushbutton Operator Console

22 mm	Price	30 mm	Price	Console Size HxWxD	Drawing Link	# Holes	Hinged
<a href="#">1490MD1</a>	\$91.00	<a href="#">1490D1</a>	\$94.00	3.53 x 3.56 x 5.06 [90 x 90 x 129]	<a href="#">PDF</a>	1	No
<a href="#">1490MD2</a>	\$106.00	<a href="#">1490D2</a>	\$111.00	3.53 x 5.81 x 5.06 [90 x 148 x 129]	<a href="#">PDF</a>	2	
<a href="#">1490MD3</a>	\$122.00	<a href="#">1490D3</a>	\$126.00	3.53 x 8.06 x 5.06 [90 x 205 x 129]	<a href="#">PDF</a>	3	
<a href="#">1490MD4</a>	\$136.00	<a href="#">1490D4</a>	\$141.00	3.53 x 10.31 x 5.06 [90 x 262 x 129]	<a href="#">PDF</a>	4	
<a href="#">1490MG4</a>	\$153.00	<a href="#">1490G4</a>	\$157.00	6.78 x 6.56 x 6.94 [172 x 167 x 176]	<a href="#">PDF</a>	4	Yes
<a href="#">1490MG6</a>	\$176.00	<a href="#">1490G6</a>	\$182.00	6.78 x 8.81 x 6.94 [172 x 224 x 176]	<a href="#">PDF</a>	6	
<a href="#">1490MG8</a>	\$199.00	<a href="#">1490G8</a>	\$206.00	6.78 x 11.06 x 6.94 [172 x 281 x 176]	<a href="#">PDF</a>	8	
<a href="#">1490MH9</a>	\$209.00	<a href="#">1490H9</a>	\$215.00	8.75 x 8.81 x 8.06 [222 x 224 x 205]	<a href="#">PDF</a>	9	
<a href="#">1490MG10</a>	\$222.00	<a href="#">1490G10</a>	\$227.00	6.78 x 13.31 x 6.94 [172 x 338 x 176]	<a href="#">PDF</a>	10	
<a href="#">1490MJ12</a>	\$233.00	<a href="#">1490G12</a>	\$250.00	6.78 x 15.56 x 6.94 [172 x 395 x 176]	<a href="#">PDF</a>	12	
<a href="#">1490MG12</a>	\$243.00	<a href="#">1490J12</a>	\$238.00	10.69 x 8.81 x 9.19 [272 x 224 x 233]	<a href="#">PDF</a>	12	
<a href="#">1490MJ16</a>	\$258.00	<a href="#">1490G16</a>	\$289.00	6.78 x 20.06 x 6.94 [172 x 510 x 176]	<a href="#">PDF</a>	16	
<a href="#">1490MG16</a>	\$281.00	<a href="#">1490J16</a>	\$265.00	10.69 x 11.06 x 9.19 [272 x 281 x 233]	<a href="#">PDF</a>	16	
<a href="#">1490MJ20</a>	\$298.00	<a href="#">1490J20</a>	\$306.00	10.69 x 13.31 x 9.19 [272 x 338 x 233]	<a href="#">PDF</a>	20	
<a href="#">1490MK25</a>	\$336.00	<a href="#">1490K25</a>	\$348.00	12.63 x 13.31 x 10.31 [321 x 338 x 262]	<a href="#">PDF</a>	25	
<a href="#">1490MK30</a>	\$367.00	<a href="#">1490K30</a>	\$380.00	12.63 x 15.56 x 10.31 [321 x 395 x 262]	<a href="#">PDF</a>	30	

Note: Dimensions in inches [millimeters].

# NEMA 12 and 13 Pushbutton Operator Consolelet



## Dimensions

