

# Enclosure Accessories

## Drip Shield Kit



### Application

- Easily installed on NEMA 12, 4, and 4X wall-mount enclosures using stainless steel bolts and sealing washers (included).
- Designed not to interfere with door clamps.
- Protects door from dripping water and settling dust.
- Constructed in 14-gauge mild steel (painted) or 316 stainless steel.
- Maintains enclosure rating.




Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Drip Shield Kit - DK Series							
ANSI 61 Gray	Price	RAL7035 Lt Gray	Price	Stainless Steel	Price	Fits Enclosure Width (in.)	Drawing Link
<a href="#">DK12GY</a>	\$62.00	<a href="#">DK12LG</a>	\$62.00	<a href="#">DK12S16</a>	\$136.00	12.0 [305]	<a href="#">PDF</a>
<a href="#">DK16GY</a>	\$68.00	<a href="#">DK16LG</a>	\$68.00	<a href="#">DK16S16</a>	\$147.00	16.0 [406]	<a href="#">PDF</a>
<a href="#">DK20GY</a>	\$74.00	<a href="#">DK20LG</a>	\$74.00	<a href="#">DK20S16</a>	\$160.00	20.0 [508]	<a href="#">PDF</a>
<a href="#">DK24GY</a>	\$81.00	<a href="#">DK24LG</a>	\$81.00	<a href="#">DK24S16</a>	\$173.00	24.0 [610]	<a href="#">PDF</a>
<a href="#">DK30GY</a>	\$91.00	<a href="#">DK30LG</a>	\$91.00	<a href="#">DK30S16</a>	\$193.00	30.0 [762]	<a href="#">PDF</a>
<a href="#">DK36GY</a>	\$99.00	<a href="#">DK36LG</a>	\$99.00	<a href="#">DK36S16</a>	\$211.00	36.0 [914]	<a href="#">PDF</a>
<a href="#">DK42GY</a>	\$110.00	<a href="#">DK42LG</a>	\$110.00	<a href="#">DK42S16</a>	\$224.00	42.0 [1067]	<a href="#">PDF</a>
<a href="#">DK48GY</a>	\$118.00	<a href="#">DK48LG</a>	\$118.00	<a href="#">DK48S16</a>	\$236.00	48.0 [1219]	<a href="#">PDF</a>
<a href="#">DK60GY</a>	\$136.00	<a href="#">DK60LG</a>	\$136.00	<a href="#">DK60S16</a>	\$276.00	60.0 [1524]	<a href="#">PDF</a>
<a href="#">DK72GY</a>	\$153.00	—	—	<a href="#">DK72S16</a>	\$307.00	72.0 [1829]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

## Pedestal Columns and Bases for Operator Consolets



Pedestal Column



Pedestal Base

### Application

- Used for floor-mounting many types of enclosures, consolets or pushbutton boxes.
- Provides wiring feature through the column.

### Pedestal Column

- Columns are formed from 14-gauge steel with 10-gauge flanges.
- Column access opening with gasketed cover.
- Columns include flange gaskets and a box connector.

### Pedestal Base

- Bases are formed from 10-gauge steel with additional reinforcing.

Pedestal Columns and Bases for Operator Consolets			
Part Number	Price	Description	Drawing Link
<a href="#">1495C35</a>	\$314.00	Straight pedestal column, carbon steel, 3500 x 400 x 400in, ANSI 61 gray, powder coat finish For use with operator consolets Flange gaskets, box connector and mounting hardware included	<a href="#">PDF</a>
<a href="#">1495D35</a>	\$470.00	Straight pedestal column, carbon steel, 3500 x 600 x 600in, ANSI 61 gray, powder coat finish For use with operator consolets Flange gaskets, box connector and mounting hardware included	<a href="#">PDF</a>
<a href="#">1495XK</a>	\$195.00	Pedestal base, carbon steel, 1800 x 1800in, ANSI 61 gray, powder coat finish For use with pedestal columns Leveling screws included	<a href="#">PDF</a>
<a href="#">1495XN</a>	\$433.00	Pedestal base, carbon steel, 2400 x 2400in, ANSI 61 gray, powder coat finish For use with pedestal columns Leveling screws included	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].