

NEMA 4, 4X, 6, and 6P Polycarbonate Flanged Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards.
- Can be used in a tabletop configuration or two different wall-mount configurations.
- Rounded corners and face provide a more modern look while still offering superior watertight ratings.
- ABS plastic or ABS versions are molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Gasketed lid with two piece tongue and groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel machine screws which are threaded into integral stainless steel bushings for repetitive assembly and disassembly. All hardware is stainless steel to avoid corrosion.
- Foot Kits available: ([1557FOOT2BK-24](#), [1557FOOT2GY-24](#), [1557FOOTGY-24](#), [1557FOOTBK-24](#))

Materials

- Available in black or gray
- UL listed polycarbonate
- Gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs

Listings

- UL94-HB for indoor or outdoor use
 - UL 508A Type 4, 4X, 6, and 6P
 - [UL File E63524]
- Complies with
 - NEMA 4, 4X, 6, and 6P
 - IEC 60529, IP68



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

NEMA 4, 4X, 6, and 6P Polycarbonate Flanged Miniature Cases with Styled Lid

Black	Light Gray	Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Replacement Gasket	Price
1557B2BK	1557B2GY	\$16.50	3.15 x 3.15 x 1.77 [80 x 80 x 45]	30 [1.18]	PDF	1557BGASKET	\$5.75
1557BA2BK	1557BA2GY	\$17.00	3.15 x 3.15 x 2.36 [80 x 80 x 60]	45 [1.77]	PDF	1557BGASKET	\$5.75
1557D2BK	1557D2GY	\$19.00	4.72 x 4.72 x 1.77 [120 x 120 x 45]	31 [1.22]	PDF	1557DGASKET	\$5.75
1557DA2BK	1557DA2GY	\$22.00	4.72 x 4.72 x 2.76 [120 x 120 x 70]	56 [2.20]	PDF	1557DGASKET	\$5.75
1557F2BK	1557F2GY	\$27.00	6.30 x 6.30 x 1.77 [160 x 160 x 45]	31 [1.22]	PDF	1557FGASKET	\$11.25
1557FA2BK	1557FA2GY	\$34.00	6.30 x 6.30 x 2.76 [160 x 160 x 70]	56 [2.20]	PDF	1557FGASKET	\$11.25
1557H2BK	1557H2GY	\$34.00	7.87 x 7.87 x 1.77 [200 x 200 x 45]	31 [1.22]	PDF	1557HGASKET	\$11.25
1557HA2BK	1557HA2GY	\$38.00	7.87 x 7.87 x 2.76 [200 x 200 x 70]	56 [2.20]	PDF	1557HGASKET	\$11.25

Notes: Dimensions in inches [millimeters].

IP66 ABS Plastic Flanged Miniature Cases with Styled Lid



Features

- Ideally suited for mounting printed circuit boards.
- Can be used in a tabletop configuration or two different wall-mount configurations.
- Rounded corners and face provide a more modern look while still offering superior watertight ratings.
 - ABS plastic or ABS Versions are molded from general purpose material which carries a flammability rating of UL94-HB. For indoor use.
- Gasketed lid with two piece tongue and groove construction provides protection against oil, dust, and water.
- Lid is secured with included M4 stainless steel machine screws which are threaded into integral stainless steel bushings for repetitive assembly and disassembly. All hardware is stainless steel to avoid corrosion.
- Foot Kits available: ([1557FOOT2BK-24](#), [1557FOOT2GY-24](#), [1557FOOTGY-24](#), [1557FOOTBK-24](#))

Materials

- Available in black or gray.
- General Purpose ABS plastic
- Gasket is one piece made from high temperature, UL listed silicone.
 - Sold in pairs

Listings

- Complies with IEC 60529, IP66



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

IP66 ABS Plastic Flanged Miniature Cases with Styled Lid

Black	Light Gray	Price	Enclosure Size HxWxD	Lid Depth	Drawing Link	Replacement Gasket	Price
1557BABK	1557BAGY	\$13.00	3.15 x 3.15 x 2.36 [80 x 80 x 60]	45 [1.77]	PDF	1557BGASKET	\$5.75
1557BBK	1557BGY	\$12.50	3.15 x 3.15 x 1.77 [80 x 80 x 45]	30 [1.18]	PDF	1557BGASKET	\$5.75
1557DABK	1557DAGY	\$19.25	4.72 x 4.72 x 2.76 [120 x 120 x 70]	56 [2.20]	PDF	1557DGASKET	\$5.75
1557DBK	1557DGY	\$14.75	4.72 x 4.72 x 1.77 [120 x 120 x 45]	31 [1.22]	PDF	1557DGASKET	\$5.75
1557FABK	1557FAGY	\$27.50	6.30 x 6.30 x 2.76 [160 x 160 x 70]	56 [2.20]	PDF	1557FGASKET	\$11.25
1557FBK	1557FGY	\$20.25	6.30 x 6.30 x 1.77 [160 x 160 x 45]	31 [1.22]	PDF	1557FGASKET	\$11.25
1557HABK	1557HAGY	\$28.50	7.87 x 7.87 x 2.76 [200 x 200 x 70]	56 [2.20]	PDF	1557HGASKET	\$11.25
1557HBK	1557HGY	\$27.50	7.87 x 7.87 x 1.77 [200 x 200 x 45]	31 [1.22]	PDF	1557HGASKET	\$11.25

Notes: Dimensions in inches [millimeters].