



Quality Products. Service Excellence.

Type 4, 4X Glass Reinforced Polyester Enclosures 1590ZGRP Series

Watertight, Thick Wall, NEMA 4X, IP66, UL Listed

Key Features:



- Molded from glass reinforced polyester. Smooth finish.
- Heavy duty thick wall design.
- Includes gasketed lid with two piece tongue and groove construction.
- C UL & UL listed under file #E65324.
- Rated IP66. Certified to NEMA 4, 4X standards per UL 508A.
- Enclosures have an impact rating of IK09 in conformity with IEC62262.
- Recommended operating temperature is -40°C to +120°C (-40°F to +248°F).
- Lid contains self-captivated stainless steel screws.
- Gasket material is EPDM sponge rubber.
- Easy wall mounting via through holes located outside of the gasket channel.
- Internal mounting shelf for bonding/mounting nuts molded in.
- Optional 16 gauge galvanized steel inner panels available.

Photo Features

Internal mounting shelf accepts inner panels or PC boards.

Lid screws become captive once installed in lid.

Wallmounting holes are located outside the gasket perimeter.



Accessories



Optional hinge kit, part number **1427HK**

- Molded from tough polyester
- Includes 12x stainless steel M4 screws and 8x o-rings.
- Mounting template included
- Note: with hinges installed, all four lid

screws are required to
maintain a proper seal

Accessories

- Pole Mount Kit
- Breather Kit
- Liquid-Tight, Strain Relief Cordgrips
- Pressure Compensation Plug
- Small Rainproof Ventilator

Part Numbers

| Part Number | Assembled Enclosure | | | | | Lid | | |
|-------------|---------------------|-------|-------|-------|-------|---------------|------------------|--------------------|
| | Length | Width | Depth | Depth | Depth | Inner Panel | Extra Lid Screws | Extra Panel Screws |
| 1590ZGRP081 | 80 | 75 | 55 | 40 | 15 | 1590ZGRP081PL | SC583-50 | SCGM4-50 |
| 1590ZGRP084 | 81 | 76 | 75 | 61 | 15 | 1590ZGRP081PL | SC583-50 | SCGM4-50 |
| 1590ZGRP082 | 110 | 75 | 55 | 40 | 15 | 1590ZGRP082PL | SC583-50 | SCGM4-50 |
| 1590ZGRP121 | 122 | 120 | 90 | 65 | 25 | 1590ZGRP121PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP083 | 160 | 75 | 55 | 41 | 15 | 1590ZGRP083PL | SC583-50 | SCGM4-50 |
| 1590ZGRP161 | 160 | 160 | 90 | 70 | 20 | 1590ZGRP161PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP131 | 190 | 75 | 55 | 40 | 15 | 1590ZGRP131PL | SC583-50 | SCGM4-50 |
| 1590ZGRP233 | 250 | 200 | 120 | 95 | 25 | 1590ZGRP233PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP123 | 220 | 120 | 91 | 66 | 25 | 1590ZGRP123PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP234 | 255 | 250 | 120 | 95 | 25 | 1590ZGRP234PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP235 | 255 | 250 | 161 | 95 | 66 | 1590ZGRP234PL | SC571-12 | SCGM6GRP-20 |
| 1590ZGRP162 | 260 | 160 | 90 | 70 | 20 | 1590ZGRP162PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP163 | 360 | 160 | 90 | 71 | 20 | 1590ZGRP163PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP243 | 400 | 250 | 120 | 95 | 25 | 1590ZGRP243PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP244 | 400 | 250 | 160 | 96 | 65 | 1590ZGRP243PL | SC571-12 | SCGM6GRP-20 |
| 1590ZGRP253 | 400 | 405 | 120 | 95 | 25 | 1590ZGRP253PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP263 | 600 | 250 | 120 | 95 | 25 | 1590ZGRP263PL | SC570-20 | SCGM6GRP-20 |
| 1590ZGRP264 | 600 | 250 | 160 | 95 | 65 | 1590ZGRP263PL | SC571-12 | SCGM6GRP-20 |

Tags: non metallic, polyester, fiberglass, NEMA, impact, IK, gasket, watertight, ZGRP

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.