



Quality Products. Service Excellence.

## DIN Rail Mounted Enclosures 1597DIN Series

### Key Features:

- Ideally suited for housing electronics for DIN rail-mounted devices. Applications include:
  - Industrial drives and controls
  - Automation
  - HVAC
  - IoT
- Mounts to standard symmetrical 35 mm DIN rail
- Dark gray mounting base molded from PPE & PS
- Light gray main enclosure body molded from polycarbonate
- Material carries a flammability rating of UL94-V0
- Designed to meet IP20
- Snap closures for easy assembly, no hardware required
- 5 models available
- 4 types of covers sold individually for use in a wide variety of applications



### Photo Features:



Mix and match covers as required



DIN rail mounting mechanism



Enclosure without covers

### Cover Options (see table below):



Closed cover



Oval cover



Vented cover



Knockout cover

Part Number	Type	Height	Width	Depth	Cover					Clear Cover
					Spaces	Closed Cover	Oval Cover	Vented Cover	Knockout Cover	
1597DINM22GY	Control Box	90	22.5	118	-	-	-	-	-	DINM22COVER
1597DIN2GY	2 Module	90	35	58	2	1597DINCOV1GY	1597DINCOV2GY	1597DINCOV3GY	1597DINCOV4GY	-
1597DIN4GY	4 Module	90	70	58	4	1597DINCOV1GY	1597DINCOV2GY	1597DINCOV3GY	1597DINCOV4GY	-
1597DIN6GY	6 Module	90	105	58	4	1597DINCOV11GY	1597DINCOV12GY	1597DINCOV13GY	1597DINCOV14GY	-
1597DIN9GY	9 Module	90	158	58	6	1597DINCOV11GY	1597DINCOV12GY	1597DINCOV13GY	1597DINCOV14GY	-

