




Quality Products. Service Excellence.

## Hard Wired 168 Series



### Features

- Single winding, does not provide isolation, for use where equipment is already isolated and only voltage change is required.
- Flexible world wide applications, 50 or 60 Hz. operation, 115VAC input.
- Output taps @ 85, 95, 105, 110, 115 and 125VAC.
- Ideal for manual line voltage adjustment for electronic equipment or small appliance operation.
- Models 168B, 168C & 168D are CSA certified (209651)
- All are UL (Type 3AH, E207860)
- Connection by flexible leads, 8" minimum length.
- Remember - These units do NOT convert line frequency



Part No.	Capacity		Overall Dimensions				Weight
	VA	A	B	C	D	E	Lbs
168B	200	3.13	3.30	3.80	2.50	1.90	4.3
168C	350	3.13	4.00	3.80	2.50	2.70	6.5
168D	500	3.75	4.00	4.60	3.00	2.80	8
168E	750	3.75	4.50	4.60	3.00	3.30	10
168F	1000	3.75	5.50	4.60	3.00	4.30	14
168H	1500	4.38	6.10	5.30	3.50	4.50	20
168J	2000	4.38	6.60	5.30	3.50	5.10	23



Tags: line transformer, autotransformer, voltage change, manual

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.