


NEMA 3R Painted Galvanized Steel Hinged Screw Cover Wall-Mount



Applications

- Designed for use as a wiring/junction box.
- Provides protection against rain, sleet, snow and dripping water.

Construction

- Formed and spot welded from 16- or 14-gauge galvanized steel.
- Drip shield top and seam-free sides, front and back.
- Stainless steel continuous hinge.
- Cover fastened with captive plated screws.
- Padlocking hasp.
- Collar studs provided for mounting optional panels.
- External mounting feet.
- Oil-resistant gaskets are permanently secured.

Finish

- Enclosure and cover are finished inside and out in ANSI 61 gray powder coating.

Listings

- UL-50 Type 3R [UL File E65324]
- CSA Type 3R [CSA File LR21001]
- Complies with
 - NEMA Type 3R
 - IEC 60529, IP24



Shipping Schedule

Same day 1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R Painted Galvanized Steel Hinged Screw Cover Wall-Mount

Part Number	Price	Enclosure Size HxWxD	Drawing Link
C3R16126HCR	\$147.00	16.33 x 12.31 x 6.34 [415 x 313 x 161]	PDF
C3R16166HCR	\$173.00	16.33 x 16.31 x 6.34 [415 x 414 x 161]	PDF
C3R18186HCR	\$257.00	18.33 x 18.31 x 6.34 [466 x 465 x 161]	PDF
C3R181810HCR	\$315.00	18.33 x 18.31 x 10.34 [466 x 465 x 263]	PDF
C3R20166HCR	\$195.00	20.33 x 16.31 x 6.34 [516 x 414 x 161]	PDF
C3R20208HCR	\$279.00	20.33 x 20.31 x 8.34 [516 x 516 x 212]	PDF
C3R24208HCR	\$310.00	24.33 x 20.31 x 8.34 [618 x 516 x 212]	PDF
C3R24248HCR	\$350.00	24.33 x 24.31 x 8.34 [618 x 617 x 212]	PDF
C3R242410HCR	\$370.00	24.33 x 24.31 x 10.34 [618 x 617 x 263]	PDF
C3R30248HCR	\$409.00	30.33 x 24.31 x 8.34 [770 x 617 x 212]	PDF
C3R302410HCR	\$712.00	30.33 x 24.31 x 10.34 [770 x 617 x 263]	PDF
C3R30308HCR	\$588.00	30.33 x 30.31 x 8.34 [770 x 770 x 212]	PDF
C3R303012HCR	\$594.00	30.33 x 30.31 x 12.34 [770 x 770 x 313]	PDF
C3R303016HCR	\$685.00	30.33 x 30.31 x 16.34 [770 x 770 x 415]	PDF
C3R362412HCR	\$543.00	36.33 x 24.31 x 12.34 [923 x 617 x 313]	PDF
C3R363012HCR	\$690.00	36.33 x 30.31 x 12.34 [923 x 770 x 313]	PDF
C3R363610HCR	\$770.00	36.33 x 36.31 x 10.34 [923 x 922 x 263]	PDF
C3R363612HCR	\$773.00	36.33 x 36.31 x 12.34 [923 x 922 x 313]	PDF
C3R423012HCR	\$761.00	42.33 x 30.31 x 12.34 [1075 x 770 x 313]	PDF
C3R423612HCR	\$869.00	42.33 x 36.31 x 12.34 [1075 x 922 x 313]	PDF
C3R483612HCR	\$965.00	48.33 x 36.31 x 12.34 [1228 x 922 x 313]	PDF
C3R483616HCR	\$1,098.00	48.33 x 36.31 x 16.34 [1228 x 922 x 415]	PDF
C3R603612HCR	\$1,156.00	60.33 x 36.31 x 12.34 [1532 x 922 x 313]	PDF

Note: Dimensions in inches [millimeters].

NEMA 3R Painted Galvanized Steel Hinged Screw Cover Wall-Mount



Shipping Schedule

Same day

1 - 15 days

Color indicates shipping lead time in business days.

NEMA 3R Painted Galvanized Steel Hinged Screw Cover Wall-Mount Subpanels

Part Number	Optional Subpanels				
	Painted	Perforated	Aluminum	Galvanized	Stainless
C3R16126HCR	18P1309	18P1309PP	18A1309	18G1309	18P1309S16
C3R16166HCR	18P1313	18P1313PP	18A1313	18G1313	18P1313S16
C3R18186HCR	18P1515	18P1515PP	—	18G1515	—
C3R181810HCR	18P1515	18P1515PP	—	18G1515	—
C3R20166HCR	18P1713	18P1713PP	—	18G1713	18P1713S16
C3R20208HCR	18P1717	18P1717PP	18A1717	18G1717	18P1717S16
C3R24208HCR	18P1717	18P1717PP	18A1717	18G1717	18P1717S16
C3R24248HCR	18P2121	18P2121PP	18A2121	18G2121	18P2121S16
C3R242410HCR	18P2121	18P2121PP	18A2121	18G2121	18P2121S16
C3R30248HCR	18P2721	18P2721PP	18A2721	18G2721	18P2721S16
C3R302410HCR	18P2721	18P2721PP	18A2721	18G2721	18P2721S16
C3R30308HCR	18P2727	18P2727PP	—	18G2727	18P2727S16
C3R303012HCR	18P2727	18P2727PP	—	18G2727	18P2727S16
C3R303016HCR	18P2727	18P2727PP	—	18G2727	18P2727S16
C3R362412HCR	18P3321	18P3321PP	18A3321	18G3321	18P3321S16
C3R363012HCR	18P3327	18P3327PP	18A3327	18G3327	18P3327S16
C3R363610HCR	18P3333	18P3333PP	—	18G3333	18P3333S16
C3R363612HCR	18P3333	18P3333PP	—	18G3333	18P3333S16
C3R423012HCR	18P3927	—	—	18G3927	18P3927S16
C3R423612HCR	18P3933	—	—	18G3933	18P3933S16
C3R483612HCR	18P4533	—	18A4533	18G4533	18P4533S16
C3R483616HCR	18P4533	—	18A4533	18G4533	18P4533S16
C3R603612HCR	18P5733	—	18A5733	18G5733	18P5733S16

Note: Dimensions in inches [millimeters].

NEMA 3R Painted Galvanized Steel Hinged Screw Cover Wall-Mount



Dimensions

