

Desktop 19-Inch Rack



Application

19 in 16-Gauge Steel Desktop Rack is perfect for small projects. Available in 6U, 8U, 12U and 16U options, this rack series is ideal for smaller IT, security, and AV applications.

Construction

- Base and panel constructed from 16-gauge steel.
- Includes two 12-gauge steel 19 in [483 mm] EIA compliant mounting rails.
 - Rails are 10-32 tapped rails with rack space indicators.
 - Rails are angled 10° when rack is assembled.
 - Starter pack of 25 rack screws included.
- Smooth black powder coat.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 195 lb [89 kg].

Features

- Available in 6U, 8U, 12U and 16U rack spacing.
- Sides of rails include multiple tie points for cable management.

Listings

- TAA compliant for GSA Schedule purchases.
- EIA compliant
- RoHS



Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

Desktop 19-Inch Racking

Part Number	Price	Rack Units	Drawing Link
HDR6UBK	\$77.00	8U	PDF
HDR8UBK	\$80.00	6U	PDF
HDR12UBK	\$88.00	12U	PDF
HDR16UBK	\$102.00	16U	PDF