



Quality Products. Service Excellence.

Low-Profile Wall Mount Rack Cabinet *HLP Series*

UL2416 rated to 200 lbs (90 kg).

TOP SELLER



Features

- Available in two (2) heights up to 41 inches of usable space and three (3) fixed rack unit options.
- Each cabinet ships with one (1) pair of 2U 180-degree rotating mounting rack rails and one (1) pair of adjustable rack rails.
 - Fixed rack mounting units are available in 4U, 6U, and 8U.
 - Fixed rails mount at five different angles, providing equipment mounting options.
 - Includes starter pack of **SCREW1032-25** screws.
- The locking hinged front door includes side venting for airflow.
 - The door and latch can be reversed to swing left to right.
 - The rear wall mounting section features conduit knockouts for 3.00", 2.00", 1.38", and 1.12" located top and bottom.
- Side venting is designed for optional 4in (120mm) fans for active cooling.
- Generous cable management lances are located on the rear section.
- Heavy-duty keyhole for wall mounting.
- Large knockouts in the rear for cable access.

Specifications

- The body and rear section are constructed of 16-gauge steel.
- Rack rails are 14-gauge steel with 10-32 tapped EIA-compliant mounting rails.
- The body includes dedicated bonding points, providing the option of drill-less mounting of electrical 4x2 utility boxes.
 - Grounding kit sold separately - **GRDKIT01** or **GRDKIT04**.
- **UL Listed 2416 load rated** to 200 lbs (90 kg).
 - *Wall Mount Racks are rated based on cabinet's weight plus the desired weight capacity to a two (2x) multiplier. 100lbs (Cabinet Weight) + 200lbs (Cabinet Load Capacity) x 2 = 600lbs. In this case, the Static Load is 600 lbs, and the UL2416 Load Rating is 200lbs.*
- The body and door are finished in rugged sand-textured RAL 9005 black or textured RAL 7035 light gray powder paint. The rack rails are finished in smooth white powder paint. Complies with the Greenguard guidelines for indoor air quality.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



Upgrade the cabinet to be dust-resistant with the **HWCF** Cabinet Sealing and Filter Kit.
Need an Outdoor Rating? [Click here.](#)

Experience the unmatched functionality of the **HLP Series Low-Profile Wall Mount Cabinet** from Hammond, designed specifically for tight spaces while delivering excellent performance. Made from durable **16-gauge steel**, the HLP cabinet features a sleek **black powder coat finish** enhancing aesthetics while providing long-lasting durability. With various sizes available (4U, 6U, and 8U), this cabinet includes a 2U **180-degree rotating mounting rail** for versatile

Low-Profile Wall Mount Rack Cabinet (HLP Series) - Hammond Mfg.

configurations and easy access to your gear. Its flexible design incorporates side venting and options for installing fans, promoting optimal airflow to keep your equipment cool. Additionally, generous cable management lances facilitate a tidy setup. Ideal for commercial applications and home offices alike, the **HLP Series** is the perfect choice for maximizing space without compromising on strength or style.

Accessories

- Universal Rack Shelf
- Hook and Loop Convenience Roll
- 10 AWG Bonding Wire Kits
- Mounting Screw and Clip Nut Combo-Pack
- Latch Replacement Kits
- Clamping Rack Shelf
- Heavy Duty Cooling Fan Kits
- Wall Rack Cabinet Sealing and Filter Kit
- We Manufacture PDUs and Outlet Strips



Part No.	Part No.	Overall Dimensions			Rack Units	Maximum Vertical Usable Depth	
		Height	Width	Depth		Pivot + Fixed	Both Rails Installed
RAL9005 Black	RAL7035 Light Gray						
HLP4U31BK	HLP4U31LG	31.00	27.50	11.15	2U + 4U	21.90	26.90
HLP4U43BK	HLP4U43LG	43.00	27.50	11.15	2U + 4U	33.90	38.90
HLP6U31BK	HLP6U31LG	31.00	27.50	15.46	2U + 6U	21.90	26.90

Part No.	Part No.	Overall Dimensions			Rack Units	Maximum Vertical Usable Depth	
		Height	Width	Depth		Pivot + Fixed	Both Rails Installed
RAL9005 Black	RAL7035 Light Gray						
HLP6U43BK	HLP6U43LG	43.00	27.50	15.46	2U + 6U	33.90	38.90
HLP8U31BK	HLP8U31LG	31.00	27.50	19.65	2U + 8U	21.90	26.90
HLP8U43BK	HLP8U43LG	43.00	27.50	19.65	2U + 8U	33.90	38.90

Optional 180-Degree Rotating Mounting Rail Kits

Part No.	Mounting Dimensions		Rack Units	Rotation	EIA Rail Type	Paint Finish
	Height	Width				
HLP2UR	3.50	19.00	2U	180 Degrees	10-32 Threaded	Smooth White
HLP4UR	7.00	19.00	4U	180 Degrees	Clip Nut Round Hole	Smooth Black
HLP6UR	10.50	19.00	6U	180 Degrees	Clip Nut Round Hole	Smooth Black
HLP8UR	14.00	19.00	8U	180 Degrees	Clip Nut Round Hole	Smooth Black

Optional Fixed Mounting Rail Kits

Part No.	Mounting Dimensions		Rack Units	Rotation	EIA Rail Type	Paint Finish
	Height	Width				
HLP2UFR	3.50	19.00	2U	Fixed five (5) positions	Threaded 10-32	Smooth White
HLP4UFR	7.00	19.00	4U	Fixed five (5) positions	Threaded 10-32	Smooth White
HLP6UFR	10.50	19.00	6U	Fixed five (5) positions	Threaded 10-32	Smooth White
HLP8UFR	14.00	19.00	8U	Fixed five (5) positions	Threaded 10-32	Smooth White

Tags: Remote Premise Box, Local Distribution Frame, Commercial Cabinet, Vertical Wallmount Cabinet, wall mounted server rack

Data subject to change without notice

© 2026. Hammond Manufacturing Ltd. All rights reserved.