



*Quality Products. Service Excellence.*

## Type 4X Stainless Steel Two Door Freestanding Enclosure HN4 FSTD SS Series

### Continuous Hinge Door with Handle



**Panel  
Sold  
Separately**



### Application

- Designed to house electrical, electronic, hydraulic or pneumatic controls and instruments
- Provides protection where equipment may be hosed down or otherwise be very wet, or in specific applications where corrosion is a serious problem.

### Construction

- Formed 12 gauge 304 stainless steel.
- Smooth, continuously welded seams without knockouts, cutouts or holes.
- Heavy duty stainless steel lifting eyebolts are provided with reinforcing support angles.
- Doors are supported with heavy gauge continuous hinges.
- Dual Access versions have doors front and back.
- 3-pt padlocking door handle.
- Seamless poured-in place gasket.
- A grounding stud is provided in the enclosure and a bonding stud is provided on the door.
- Center post is removable for easy installation of the inner panel.

### Standards

- UL 508A Type 3R, 4X and 12
- CSA Type 3R, 4X and 12
- Complies with:
  - NEMA Type 3R, 4X, 12 and 13
  - IEC 60529, IP66

### Finish

- Cover and enclosure are natural stainless steel with a smooth brushed finish.

### Accessories

- Inner Panels
- Panel Rails
- Door Stop Kit
- Drip Shield Kit
- Window Kits
- Lighting
- Center Panel Supports
- Swing Out Frames
- Top Hat Cable Modules
- Type 12/4, 4X Handle Kits
- Climate Control
- General Accessories

### Single Access

| Part No.      | Enclosure |       |       | Optional Full Panel <sup>1</sup> |
|---------------|-----------|-------|-------|----------------------------------|
|               | H         | W     | D     |                                  |
| HN4FS604818SS | 60.00     | 48.00 | 18.00 | 60AWFW                           |
| HN4FS724818SS | 72.00     | 48.00 | 18.00 | 72ZFW                            |

| Enclosure     |       |       |       |                                  |
|---------------|-------|-------|-------|----------------------------------|
| Part No.      | H     | W     | D     | Optional Full Panel <sup>1</sup> |
| HN4FS726018SS | 72.00 | 60.00 | 18.00 | 72ZXFW                           |
| HN4FS727218SS | 72.00 | 72.00 | 18.00 | 72ZYFW                           |
| HN4FS904820SS | 90.00 | 48.00 | 20.00 | 90BWFW                           |
| HN4FS907220SS | 90.00 | 72.00 | 20.00 | 90BYFW                           |
| HN4FS724824SS | 72.00 | 48.00 | 24.00 | 72ZWFW                           |
| HN4FS726024SS | 72.00 | 60.00 | 24.00 | 72ZXFW                           |
| HN4FS727224SS | 72.00 | 72.00 | 24.00 | 72ZYFW                           |
| HN4FS907224SS | 90.00 | 72.00 | 24.00 | 90BYFW                           |
| HN4FS726036SS | 72.00 | 60.00 | 36.00 | 72ZXFW                           |
| HN4FS907236SS | 90.00 | 72.00 | 36.00 | 90BYFW                           |

<sup>1</sup> Refers to optional full height/full width panels. Depth panels/half height width panels are also available

Dual Access

| Enclosure       |       |       |       |                                  |
|-----------------|-------|-------|-------|----------------------------------|
| Part No.        | H     | W     | D     | Optional Full Panel <sup>1</sup> |
| HN4FS724824DASS | 72.00 | 48.00 | 24.00 | 72ZWFW                           |
| HN4FS726024DASS | 72.00 | 60.00 | 24.00 | 72ZXFW                           |
| HN4FS727224DASS | 72.00 | 72.00 | 24.00 | 72ZYFW                           |
| HN4FS907224DASS | 90.00 | 72.00 | 24.00 | 90BYFW                           |
| HN4FS726036DASS | 72.00 | 60.00 | 36.00 | 72ZXFW                           |

<sup>1</sup> Refers to optional full height/full width panels. Depth panels/half height width panels are also available

Tags: **HN4FS, freestanding, stainless, stainless steel, 304, control box, Type 4X, two door, NEMA 4X,** *Data subject to change without notice*  
**continuous hinge, handle, corrosion**